10" Gigabit Ethernet Switch 8 Port + 1 SFP

Description

This Gigabit Ethernet Switch by Delock can be used to connect different network components. In addition, the built-in SFP slot allows you to expand the network with a fiber optic connection.

10” rack mounting
With the supplied mounting brackets, the hub can be mounted in a 10″ rack.



Item no. 88064

EAN: 4043619880645

Country of origin: China

Package: White Box

Technical details

- Connectors:
  8 x RJ45 jack for 10/100/1000 Mbps Base-T
  1 x SFP slot for 1 Gbps SFP module
  (SFP module not included)
  1 x IEC C14 connector
- Data transfer rate up to 1 Gb/s
- Supports IEEE 802.3 / 802.3u / 802.3z / 802.3ab
- LEDs for status monitoring
- VLAN (port isolation or 1:1 mode) selectable by DIP switch
- 330 m long range mode with 10 Mb/s
- Robust metal housing
- Fanless
- Internal power supply
- Power consumption: max. 10 W
- Operating temperature: -20 °C ~ 60 °C
- Dimensions (LxWxH): ca. 254 x 115 x 44 mm

System requirements

- Device with one free RJ45 port

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Package content

- Switch
- 10" mounting brackets
- Wall mounting brackets
- 4 x screw
- Power cord
- User manual

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Mounting type:	wall 10 in

Interface

Output:	8 x RJ45 jack
Input:	1 x SFP jack 1 x IEC C14 connector

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 1 Gbps
Operating temperature:	-20 °C ~ 60 °C

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	254 mm
Width:	115 mm
Height:	44 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**