

ESD Fleece Jackets

ESD High Visibility Vests



88% Polyester and 12% conductive fiber

Weight: 300g/m2


Closure and 2-side pockets with zipper

ESD-sign at left front side

Unisex sizes: S - 3XL (others on request)

Custom logos and staff names on request

Size	Navy Blue	Grey
S	STC60225252	STC60210102
M	STC60225253	STC60210103
L	STC60225254	STC60210104
XL	STC60225255	STC60210105
2XL	STC60225256	STC60210106
3XL	STC60225257	STC60210107



Resistivity point-point (Rp): 10⁶- 10⁷Ohms
Decay time: < 2 seconds
Conforms to current ESD Standards;
IEC61340-5-1 & ANSI/ESD S20.20

Size	A	B	C	D	E
S	48	52	52	63	68
M	50	55	55	64	70
L	51	57	57	65	71
XL	53	59	59	66	73
2XL	54	63	63	67	74
3XL	56	67	67	68	76

The electrical properties are retained,
even after 50 industrial washes.

- Wash at maximum 40°C
- Ironing at maimum 110°C
- Do not bleach
- Do not dry clean
- Do not tumble dry
- Do not use fabric softners



98% Polyester and 2% carbon coated yan

Weight: 120 g/m2

Static dissipative vest for use in ESD protected areas


Lightweight breathable and comfortable flt

Closes with 2 velcro fastening strips

2 „all around” reflector strips

ESD-sign at left front side

Size	Yellow
M	STC80070701
	* fits XS to L
2XL	STC80070702
	* fits XL to 3XL



Resistivity point-point (Rp): 10⁶- 10⁷Ohms
Decay time: < 2 seconds
Conforms to current ESD Standards;
IEC61340-5-1 & ANSI/ESD S20.20

Size	A	B	C
M	62	14	64
2XL	68	16	70

The electrical properties are retained,
even after 50 industrial washes.

- Wash at maximum 40°C
- Ironing at maimum 110°C
- Do not bleach
- Do not dry clean
- Do not tumble dry
- Do not use fabric softners