
# KEMET Part Number: T598B225M035AHS200

T598, Tantalum, Polymer Tantalum, 2.2 uF, 20%, 35 VDC, SMD, Polymer, Molded, Low ESR, AEC-Q200, 200 mOhms, 3528, Height Max = 2.1mm




| General Information | |
|---|---|
| **Series:** | T598 |
| **Dielectric:** | Polymer Tantalum |
| **Style:** | SMD Chip |
| **Description:** | SMD, Polymer, Molded, Low ESR, AEC-Q200 |
| **Features:** | Automotive |
| **RoHS:** | No |
| **Prop 65:** | **WARNING:** Cancer and reproductive harm - www.p65warnings.ca.gov. |
| **REACH:** | SVHC (Pb – CAS 7439-92-1) |
| **Termination:** | Solder Coated |
| **Qualifications:** | AEC-Q200 |
| **AEC-Q200:** | Yes |
| **Shelf Life:** | 52 Weeks |
| **MSL:** | 3 |

| Dimensions | |
|---|---|
| **Footprint** | 3528 |
| **L** | 3.5mm +/-0.2mm |
| **W** | 2.8mm +/-0.2mm |
| **H** | 1.9mm +/-0.2mm |
| **T** | 0.13mm REF |
| **S** | 0.8mm +/-0.3mm |
| **F** | 2.2mm +/-0.1mm |
| **A** | 1.1mm MIN |
| **B** | 0.4mm +/-0.15mm |
| **P** | 0.5mm REF |
| **R** | 1mm REF |
| **X** | 0.1mm +/-0.1mm |

| Specifications | |
|---|---|
| **Capacitance:** | 2.2 uF |
| **Capacitance Tolerance:** | 20% |
| **Voltage DC:** | 35 VDC (105C), 23.45 VDC (125C) |
| **Temperature Range:** | -55/+125°C |
| **Rated Temperature:** | 105°C |
| **Humidity:** | 85C, 85% RH, load, 1000 Hours |
| **Dissipation Factor:** | 8% 120Hz 25C |
| **Failure Rate:** | N/A |
| **Resistance:** | 200 mOhms (100kHz 25C) |
| **Ripple Current:** | 797 mA (rms, 100kHz 45C), 717.3 mA (rms, 85C), 199.2 mA (rms, 125C) |
| **Leakage Current:** | 7.7 uA (5min 25°C) |

| Packaging Specifications | |
|---|---|
| **Weight:** | 94.85 mg |
| **Packaging:** | T&R, 178mm |
| **Packaging Quantity:** | 2000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2020 KEMET