

Antenna Cable SMA jack bulkhead to I-PEX Inc., MHF® I plug 1.13 10 cm thread length 10 mm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 67413

EAN: 4043619674138

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA jack bulkhead
 - 1 x I-PEX Inc., MHF® I plug
- Frequency range: DC - 6 GHz
- Insulation resistance: 500 MΩ / DC 500 V
- Thread length: 10 mm
- Impedance: 50 Ohm
- Cable type: 1.13
- Cable type: coaxial
- Cable attenuation:
 - 3.8 dB @ 3 GHz per meter
 - 5.4 dB @ 6 GHz per meter
- Cable diameter: ca. 1.13 mm
- Cable colour: black
- Smallest bending radius: 4.5 mm
- Operating temperature: -40 °C ~ 75 °C
- Cable length incl. connectors: ca. 10 cm

System requirements

- Device with one free SMA or I-PEX Inc., MHF® I port

Package content

- Cable
- 1 x nut
- 1 x serrated lock washer

Interface

Connector 1:	1 x SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Thread length:	10 mm
Cable category:	coaxial
Cable type:	1.13
Cable attenuation:	3.2 dB @ 2.4 GHz per meter
Cable colour:	black
Cable length incl. connectors:	10 cm
Smallest bending radius:	4.5 mm
Cable diameter:	1.13 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

