

DATA SHEET

SUNGMUN CODE : NSIL-10S-TR
DESCRIPTION : SLIDE SWITCH









SUNGMUN ELECTRONICS CO., LTD.

Address 301-302,Bucheon Technopark 345, Seokcheon-ro, Ojeong-gu
Bucheon-si, Gyeonggi-do, Korea
TEL. +82-32-328-1941~4
FAX +82-32-328-1945
E-mail sungmun@sungmun.co.kr
Website www.sungmun.com

REV. NO.	DATE	REVISION	DR	CH	APP
△	22.12.16	CHANGE THE MARKING / DRAW NO	H.S LEE	K.N KIM	W.J LEE
△	23.10.13	DIN ISO-2768-1m tolerance applied	H.S LEE	K.N KIM	W.J LEE

SPECIFICATION

1. Rating : DC12V 0.5A~24V 0.3A.
2. Contact Resistance : 30mΩ Max.
3. Travel : 1.6mm.
4. Operating Force : 250gf ± 150gf.
5. Life Cycle : 2,000 Cycle (with load).
6. Packing : 200pcs Vinyl Bag / 700pcs Reel Packing



DIN ISO-2768-1m					DRAW/DESIGNED		CHECKED		APPROVED				TITLE		MINI SLIDE SWITCH		REV.		
H.S LEE		K.N KIM		W.J LEE		UNIT		SCALE		MODEL NO.									
Ranges		0.5~3		3~6		6~30		30~120		120~400		mm		3:1		DRAW NO.		03	
Tolerance		± 0.1		± 0.1		± 0.2		± 0.3		± 0.5		A4		NSIL-10S-03					
 SUNGUMUN ELECTRONICS CO.,LTD																			

1. Electrical Characteristics :

- 1.1 Rating : AC, DC 12V 0.5A~24V 0.3A (Minimum current: 1mA)
- 1.2 Contact Resistance : Max 30 mΩ
- 1.3 Insulation Resistance : Min 10,000 MΩ at DC 500V
- 1.4 Withstanding Voltage : 1min at AC 500V

2. Mechanical Characteristics :

- 2.1 Operating Force : 250gf ± 150gf
- 2.2 Travel : 1.6mm
- 2.3 Insulator :
 - 2.3.1 Case : Glass Fiber resin
 - 2.3.2 Slide : Glass Fiber resin
- 2.4 Terminal : Nickel, Gold Plate

3. Life Test :

- 3.1 Test Condition : Operations at a rate of 15-20 cycles in 1 minute
 - 3.1.1 With load : 2,000 cycles
 - 3.1.2 Without load : 10,000 cycles
- 3.2 Operating Force : With +40%, -40% of Initial Value
- 3.3 Contact Resistance : Max 200mΩ

4. Environmental Characteristics :


- 4.1 Operating Temperature : -40°C to +85°C
- 4.2 Storage Temperature : -40°C to +85°C
- 4.3 Humidity Test :
 - 4.3.1 Test Conditions : Measured 1hour after exposure to ambient
After 96hours exposure at 40±2°C, 90-95% R.H
 - 4.3.2 Insulation Resistance : Min 100MΩ, at DC 500V
 - 4.3.3 Withstanding Voltage : 1min at AC 250V

5. Solder Conditions :

5.1 Hand Solder : 3~4 sec. at 350°C (Dipping type)

5.2 Wave Solder : 5 sec. at 260°C (Dipping type)



5.3 Reflow Solder (SMD type)



5.3.1 Condition for Soldering

Profile Feature	Pb-Free Assembly
Average Ramp-UP Rate($T_s \text{ max}$ to T_P)	3°C/second max
Preheat - Temperature Min($T_s \text{ min}$) - Temperature Max($T_s \text{ max}$) - Time ($t_s \text{ min}$ to $t_s \text{ max}$)	150°C 200°C 60-180seconds
Time maintained above: - Temperature (T_L) - Time (t_L)	217°C 60-150seconds
Peak/Classification Temperature(T_P)	260°C +0°C/ -5°C
Time within 5°C of actual Peak Temperature(T_P)	5~10 seconds
Ramp-Down Rate	6°C/sec max
Time 25°C to Peak Temperature	8 minutes max

REV. NO.	DATE	REVISION	DR	CH	APP
Δ	23.10.13	Recreation of drawings for unification of drawing formats	H.S LEE	K.M KIM	W.J LEE



REEL	TYPE	COLOR	HUB	SIZE
	PLASTIC	BLACK	80	330
SHEET	BLACK 24MMX0.4	PACKING QUANTITY	700/REEL	

- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOL ± 0.2
 2. CAMBER NOT TO EXCEED 1mm IN 250mm.
 3. MATERIAL : BLACK CONDUCTIVE POLYSTYRENE.
 4. KO MEASURED FROM A PLANE ON THE INSIDE BOTTOM OF THE POCKET TO THE TOP SURFACE OF THE CARRIER.
 5. POCKET POSITION RELATIVE TO SPROCKET HOLE MEASURED AS TRUE POSITION OF POCKET, NOT POCKET HOLE.
 6. ALL DIMENSIONS ARE IN MILLIMETERS.

DECIMALS ANGULAR
X.X ± 0.13 $\pm 1^\circ$
X.XX ± 0.10

DRAW/DESIGNED	CHECKED	APPROVED	G.TOL		TITLE
W.J LEE	J.P ROH	K.I LEE	---	---	MSI Series SMD Reel Packing
2019-04-12	2019-04-12	2019-04-12	UNIT	SCALE	MODEL
			mm	N:S	NO.
SUNGJUN ELECTRONICS CO.,LTD			SIZE	DRAW	NO.
			A4	NO.	
			TR-MS10-00S-02		REV.
					02