


PX9117



Pressure transmitter with ceramic measuring cell

PA-001PRBN14-B-DVG/US/ IV



1 ventilation



Product characteristics	
Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [psi]	0...15
Process connection	threaded connection 1/4" NPT external thread internal thread:M5
Application	
Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Medium temperature [°C]	-25...90
Min. bursting pressure [psi]	450
Min. bursting pressure [MPa]	3.1
Pressure rating [psi]	145
Pressure rating [MPa]	1
Type of pressure	relative pressure
Electrical data	
Operating voltage [V]	16...32 DC
Current consumption [mA]	< 18
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 1



Pressure transmitter with ceramic measuring cell

PA-001PRBN14-B-DVG/US/ IV

Outputs		
Total number of outputs		1
Output signal		analogue signal
Number of analogue outputs		1
Analogue voltage output [V]		0...10
Min. load resistance [Ω]		2000
Overload protection		yes
Measuring/setting range		
Measuring range [psi]		0...15
Accuracy / deviations		
Repeatability [% of the span]		< 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the span]		< $\pm 0,25$ (BFSL) / < $\pm 0,5$ (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Long-term stability [% of the span]		< $\pm 0,05$; (per 6 months)
Temperature coefficient zero point [% of the span / 10 K]		0,15; (0...80 °C)
Temperature coefficient span [% of the span / 10 K]		0,2; (0...80 °C)
Response times		
Step response time analogue output [ms]		3
Operating conditions		
Ambient temperature [°C]		-25...80
Storage temperature [°C]		-40...100
Protection		IP 65
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	30 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted radiation of interference	10 V
	immunity	according to the automotive directive 2004/104/EC / CISPR 25
	HF radiated	100 V/m
	pulse resistance	ISO 7637-2 / severity level 3
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF [years]		550
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight [g]		211.5
Housing		cylindrical
Dimensions [mm]		$\varnothing 30$ / L = 79.5

PX9117



Pressure transmitter with ceramic measuring cell

PA-001PRBN14-B-DVG/US/ /V

Materials	stainless steel (316L/1.4404); FKM; PA; EPDM/X
Materials (wetted parts)	stainless steel (303/1.4305); ceramics; FKM
Min. pressure cycles	100 million
Process connection	threaded connection 1/4" NPT external thread internal thread:M5
Restrictor element integrated	no (can be retrofitted)

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

