

Adapter cable USB Type-A to Serial RS-232 RJ12 with ESD protection Leadshine 2 m

Opis

This USB to serial RS-232 RJ12 adapter cable by Delock is suitable with the ProTuner software for configuration, control, monitoring etc. of the servo and stepper motors by Leadshine.

Compatible Devices:

Stepper motors:

DM432C, DM442, DM556, DM856 3DM683 AM882 DM1182 DM2282

Servomotors:

DCS810, DCS810S, ACS306, ACS606, ACS806



Numer artykułu 66737

EAN: 4043619667376

Kraj pochodzenia: China

Opakowanie: Torba na zamek błyskawiczny

Szczegóły techniczne

- Connectors:
1 x USB 2.0 Type-A male
1 x Serial RS-232 RJ12 plug
- Chipset: FTDI FT231X
- Plug & Play
- ESD protection:
- FIFO: 512 Byte - TX
- FIFO: 512 Byte - RX
- Compatible with USB 3.0, USB 2.0, and USB 1.1 full speed 12 Mbps
- Data transfer rate up to 230.4 Kb/s
- Signals: RXD(3), GND(4), TXD(5)
- ESD protection IEC 61000-4-2
HCP & VCP: ± 4 kV
Air Discharge: ± 8 kV
Contact Discharge: ± 4 kV
- Colour: black
- Cable length incl. connectors: ca. 2.0 m
- Suitable for various devices by Leadshine


Wymagania systemowe

- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Zawartość opakowania

- Adapter cable USB 2.0 Type-A to RS-232 RJ12

Zdjęcia



Ogólne

Specyfikacja:	RS-232 (EIA / TIA) USB 2.0
Obsługiwany system operacyjny:	Windows 10 32-bit Windows 10 64-bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interfejs

Złącze 1:	1 x USB 2.0 Typ-A męski
Złącze 2:	1 x RJ12 męski

Właściwości techniczne

Chipset:	FTDI FT231XS
Szybkość transmisji danych:	230,4 Kbps
FIFO:	512 byte
Transmisja sygnału:	TxD, RxD und GND
UART:	USB to serial UART

Właściwości fizyczne

Długość kabla ze złączem:	2 m
Kolor:	czarny
Ochrona przed przepięciami:	±8 kV EN / IEC 61000-4-2 Air Gap Discharge ±4 kV EN / IEC 61000-4-2 Contact Discharge ±4 kV EN / IEC 61000-4-2 VCP & HCP

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de