



ST - ICT Test Probe

mm [inch]




ST1000 CC54 N

Minimum centers: 2.54 [.100]
 Full travel: 6.35 [.250]
 Working travel: 4.30 [.169]
 Current rating: 8 A
 Probe resistance: < 20mΩ
 Operating temperature: -40°C up to +120°C
 Plunger material: Steel / Gold plated
 Barrel material: PhBr / Gold plated
 Spring material: Stainless Steel

Spring force at working stroke: 2.0 N [7.2 oz]

© COPYRIGHT 2023 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST1000 CC54 N		
	Designed	M.K.	2023.10.27	Drawing No.:		
	Drawn					
	Checked					
	Note				A4	SHEET 1 OF 2

ST - ICT Test Probe



Tools for the Test Probe

Tool Handle: TH1
Universal Insertion Bit: TBP10000
Insertion Bit: TBP10070

Tools for the Receptacle

Tool Handle Insertion: TH1
Tool Handle Insertion/Extraction: TH2
Universal Insertion Bit: TBP10000
Insertion Bit: TBR10035
Extraction Bit: TBR10070

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED		Name	Date	Catalog Item: ST1000 CC54 N			
	Designed	M.K.	2024.05.20	Drawing No.:			
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Drawed						
	Checked						
	Note					A4	SHEET 2 OF 2
				 TEST · SUPPORT · INNOVATE			