
CEDM7001

SURFACE MOUNT SILICON N-CHANNEL ENHANCEMENT-MODE MOSFET



Top View Bottom View

SOT-883L CASE

www.centralsemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CEDM7001 is an N-Channel Enhancement-mode silicon MOSFET, manufactured by the N-Channel DMOS Process, designed for high speed pulsed amplifier and driver applications. This MOSFET offers low $r_{DS(ON)}$ and low theshold voltage.

MARKING CODE: H

COMPLEMENTARY P-CHANNEL: CEDM8001

FEATURES:

- 100mW Power Dissipation
- 0.4mm low package profile
- Low $r_{DS(ON)}$
- Low threshold voltage
- Logic level compatible
- Small leadless surface mount package

APPLICATIONS:

- Load/Power switches
- DC - DC converters
- Battery powered portable equipment

MAXIMUM RATINGS: (T_A=25°C)	**SYMBOL**		**UNITS**
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	10	V
Continuous Drain Current (Steady State)	I_D	100	mA
Peak Drain Current, tp=10μs	I_{DM}	200	mA
Power Dissipation	P_D	100	mW
Operating and Storage Junction Temperature	T_J, T_{stg}	-65 to +150	°C

ELECTRICAL CHARACTERISTICS: (T_A=25°C unless otherwise noted)


SYMBOL	**TEST CONDITIONS**	**MIN**	**TYP**	**MAX**	**UNITS**
I_{GSSF}, I_{GSSR}	V_{GS}=10V, V_{DS}=0			1.0	μA
I_{DSS}	V_{DS}=20V, V_{GS}=0			1.0	μA
BV_{DSS}	V_{GS}=0, I_D=100μA	20			V
$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=250μA	0.6		0.9	V
$r_{DS(ON)}$	V_{GS}=4.0V, I_D=10mA		0.9	3.0	Ω
$r_{DS(ON)}$	V_{GS}=2.5V, I_D=10mA		1.3	4.0	Ω
$r_{DS(ON)}$	V_{GS}=1.5V, I_D=1.0mA			15	Ω
g_{FS}	V_{DS}=10V, I_D=100mA	100			mS
C_{rss}	V_{DS}=3.0V, V_{GS}=0, f=1.0MHz		4.0		pF
C_{iss}	V_{DS}=3.0V, V_{GS}=0, f=1.0MHz		9.0		pF
C_{oss}	V_{DS}=3.0V, V_{GS}=0, f=1.0MHz		9.5		pF
$Q_{g(tot)}$	V_{DS}=10V, V_{GS}=4.5V, I_D=100mA		0.566		nC
Q_{gs}	V_{DS}=10V, V_{GS}=4.5V, I_D=100mA		0.16		nC
Q_{gd}	V_{DS}=10V, V_{GS}=4.5V, I_D=100mA		0.08		nC
t_{on}	V_{DD}=3.0V, V_{GS}=2.5V, I_D=10mA		50		ns
t_{off}	V_{DD}=3.0V, V_{GS}=2.5V, I_D=10mA		75		ns

R9 (19-September 2014)

CEDM7001

SURFACE MOUNT SILICON N-CHANNEL ENHANCEMENT-MODE MOSFET

SOT-883L CASE - MECHANICAL OUTLINE



DIMENSIONS				
	INCHES		MILLIMETERS	
SYMBOL	MIN	MAX	MIN	MAX
A	0.014		0.35	
B	0.037	0.041	0.95	1.05
C	0.022	0.026	0.55	0.65
D	0.026		0.65	
E	0.000	0.002	0.00	0.05
F	0.012	0.016	0.30	0.40
G	0.005	0.007	0.13	0.18
H	0.008	0.012	0.20	0.30
J	0.018	0.022	0.45	0.55
K	0.008	0.012	0.20	0.30

SOT-883L (REV:R2)

LEAD CODE:
1) Gate
2) Source
3) Drain

MARKING CODE: H

Package Type Options (all dimensions are maximum - in mm)


Package	Length	Width	Height	P_D (mW)	Central Item Number
SOT-883L	**1.05**	**0.65**	**0.40**	**100**	**CEDM7001**
SOT-883VL	1.05	0.65	0.32	100	CEDM7001VL
SOT-953	1.05	1.05	0.50	250	CMNDM7001
SOT-523	1.70	1.70	0.78	250	CMUDM7001

CEDM7001


SURFACE MOUNT SILICON N-CHANNEL ENHANCEMENT-MODE MOSFET

TYPICAL ELECTRICAL CHARACTERISTICS


Output Characteristics




Drain Source On Resistance




Capacitance



Transfer Characteristics



Power Derating



R9 (19-September 2014)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES

PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centralsemi.com

Worldwide Field Representatives:
www.centralsemi.com/wwreps

Worldwide Distributors:
www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centralsemi.com/terms