



Passive Components > Resistors > Chassis Mount Resistors > Wirewound Resistor: Mineral, 2.5 Kw



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **1 Ω**

Power Rating: **2000 W**

Element Type: **Wire Wound**

[All Wirewound Resistor: Mineral, 2.5 Kw \(607\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	2500 V
Resistance Class	Up to 1kΩ
Resistance Value	1 Ω
Power Rating	2000 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Solder Lug

Mechanical Attachment

Panel Mount Feature Type	Mounting Brackets
--------------------------	-------------------

Dimensions

--	--



Product Height	119 mm[4.685 in]
Product Length	560 mm[22.047 in]
Product Width	60 mm[2.362 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±440 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE2000B1R0J

1 ohm, Wire Wound, 5 %, Power Resistor, 2000 W, 2 Terminations, ±440 ppm/°C, Solder Lug, Loose Piece - Box, 119 mm [4.685 in] Height, CGS TE





TE Part # CAT-C339-T2201
Wirewound Resistor: Mineral, 2.5 Kw



TE Part # 2176438-1
TE 2000W RESISTOR SET 1 X 12
VALUES 5%

Also in the Series | CGS TE



Chassis Mount Resistors(667)



RJ14 Connectors(4)



RJ22 Connectors(2)



RJ25 Connectors(4)



RJ45 Connectors(27)


Customers Also Bought



TE Part #1SNK505210R0000
ZS4-D2



TE Part #1-338310-2
15POS.HD20 PLUG ASS'Y




TE Part #3-770060-1
MINI AMP-IN PTLP/PHBZ




TE Part #1825027-8
FSMRA3JH04=R/A,TACT PB SW,160G




TE Part #9-1879215-2
CPF 0402 41K2 0.1% 25PPM 1K RL



TE Part #1958430-1
TERMINAL,STRATO, HR, R, 1/0HD, 5
/16 STUD



TE Part #2176079-1
EP 3W 10R 5%



TE Part #3-2176243-3
CRGS0603 5% 470R



Documents

Product Drawings

TE 2000W 1R0 5% Bracket

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1879456-1_BB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1879456-1_BB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1879456-1_BB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

High Power Wire wound Resistor Type TE Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English