

Media Converter 100Base-FX SC MM 1310 nm 2 km

Description

This Delock Fast Ethernet Media Converter can be used to expand your network by an optical fiber interface.



Item no. 86216

EAN: 4043619862160

Country of origin: China

Package: White Box

Technical details

- For Multi-Mode-Fiber, 1310 nm wavelength
- Distance up to 2 km with 50/125 µm fiber
- Connector:
 - SC Duplex connector for 100 Base-FX
 - RJ45 connector for 10/100 Base-TX
- Transmission rate up to 100 Mb/s
- 6 LEDs for status monitoring
- DIP-Switch for configuration of LFP (Link Fault Pass Through),
 - Half- or Full-Duplex, 10 or 100 Mb/s mode
- Power supply with 5 V included
- Power consumption: 2,5 W
- Dimensions (LxWxH): ca. 95 x 70 x 26 mm

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: KA0601A-0501000EU
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.2 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W
- Average active efficiency: 75.5 %
- No-load power consumption: 0.09 W

- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

Package content

- Media Converter
- Power supply
- User manual

Images



Interface

Output:	1 x RJ45 jack
Input:	1 x SC Duplex female

Technical characteristics

Data transfer rate:	Fast Ethernet up to 100 Mbps
Operating temperature:	0 °C ~ 55 °C

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	94 mm
Width:	71 mm
Height:	26 mm

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.2 A
Power supply output:	5.0 V / 1.0 A

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

