






Clamping force by 16,2 mm $\approx$ 30N.

UN - D1041		TOLERANCES UNLESS OTHERWISE STATED			
		DIMENSION $\pm$	ANGLE $\pm$		
GENERAL ROUGHN.	UNIT mm	MATERIAL Steel SK7 Wnr.: 1.1740		ASSEMBLY NO.	
SCALE 5:1	PROJ. EUROP.	TREATMENT Ni flash (thickness 0,5 μ m), Sn plated (thickness >4 μ m). Solderability: IEC 60 068-2-20 Part 2. Test Ta, method 1		PATTERN NO.	
CLASS.NO.		CLI/P-RM10/I		ORDER NO./ORDERNR	
				QUANT	
				5	
				4	
				3	
				2 26.02.2024.	
				1 27.02.2007.	
NAME F. Lach.		SUPERS.	DATE: 22.02.1991.	Property of FERROXCUBE Polska Sp. z o.o.	
FILE NAME: CLI_P-RM10_112.idw				PAGE GROUP: 112	
				PAGES: / 1	

4322 021 34321