



mm [inch]




Minimum centers:	2.54 [.100]
Full travel:	6.35 [.250]
Working travel:	4.30 [.169]
Current rating:	8 A
Probe resistance:	< 20mΩ
Operating temperature:	-40°C up to +120°C
Plunger material:	BeCu / Gold plated/Plastic tip
Barrel material:	PhBr / Gold plated
Spring material:	Stainless Steel

Spring force at working stroke: 3.0 N [10.8 oz]

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item:		
	Designed	M.K.	2024.09.11	ST1000 DC94 LX		
	Drawn			Drawing No.:		
	Checked					
	Note					
					A4	SHEET 1 OF 2

ST - ICT Test Probe



Tools for the Test Probe

Tool Handle: TH1
Universal Insertion Bit: TBP10000
Insertion Bit: TBP10070

Tools for the Receptacle

Tool Handle Insertion: TH1
Tool Handle Insertion/Extraction: TH2
Universal Insertion Bit: TBP10000
Insertion Bit: TBR10035
Extraction Bit: TBR10070

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST1000 DC94 LX			
	Designed	M.K.	2024.09.11	Drawing No.:			
	Drawed						
	Checked						
Note					A4	SHEET 2 OF 2	EQUIPTEST TEST - SUPPORT - INNOVATE