

Switch-mode Series NPN Silicon Power Transistor

BUV22

This device is designed for high speed, high current, high power applications.

Features

- High DC Current Gain:
 $h_{FE} \text{ min} = 20 \text{ at } I_C = 10 \text{ A}$
- Low $V_{CE(sat)}$, $V_{CE(sat)}$
 $\text{max} = 1.0 \text{ V at } I_C = 10 \text{ A}$
- Very Fast Switching Times:
 $T_F \text{ max} = 0.35 \mu\text{s at } I_C = 20 \text{ A}$
- Pb-Free Package is Available*

MAXIMUM RATINGS

Symbol	Rating	Value	Unit
$V_{CEQ(SUS)}$	Collector-Emitter Voltage	250	Vdc
V_{CBO}	Collector-Base Voltage	300	Vdc
V_{EBO}	Emitter-Base Voltage	7	Vdc
V_{CEX}	Collector-Emitter Voltage ($V_{BE} = -1.5 \text{ V}$)	300	Vdc
V_{CER}	Collector-Emitter Voltage ($R_{BE} = 100 \Omega$)	290	Vdc
I_C I_{CM}	Collector-Current – Continuous – Peak ($PW \leq 10 \text{ ms}$)	40 50	Adc Apk
I_B	Base-Current Continuous	8	Adc
P_D	Total Device Dissipation @ $T_C = 25^\circ\text{C}$	250	W
T_J, T_{stg}	Operating and Storage Junction Temperature Range	-65 to 200	$^\circ\text{C}$


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Characteristics	Max	Unit
θ_{JC}	Thermal Resistance, Junction-to-Case	0.7	$^\circ\text{C/W}$

*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, [SOLDDRRM/D](#).

**40 AMPERES
NPN SILICON POWER
METAL TRANSISTOR
250 VOLTS – 250 WATTS**



TO-204AE (TO-3)
CASE 197A

MARKING DIAGRAM



BUV22 = Device Code
G = Pb-Free Package
A = Assembly Location
Y = Year
WW = Work Week
MEX = Country of Origin

ORDERING INFORMATION

Device	Package	Shipping
BUV22G	TO-204 (Pb-Free)	100 Units / Tray

DISCONTINUED (Note 1)

BUV22	TO-204	100 Units / Tray
-------	--------	------------------

1. **DISCONTINUED:** This device is not recommended for new design. Please contact your **onsemi** representative for information. The most current information on this device may be available on www.onsemi.com.

BUV22

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Characteristic	Min	Max	Unit
--------	----------------	-----	-----	------

OFF CHARACTERISTICS (Note 2)

$V_{CE(sus)}$	Collector-Emitter Sustaining Voltage ($I_C = 200\text{ mA}$, $I_B = 0$, $L = 25\text{ mH}$)	250	–	Vdc
I_{CEX}	Collector Cutoff Current at Reverse Bias ($V_{CE} = 300\text{ V}$, $V_{BE} = -1.5\text{ V}$) ($V_{CE} = 300\text{ V}$, $V_{BE} = -1.5\text{ V}$, $T_C = 125^\circ\text{C}$)		3.0 12.0	mAdc
I_{CEO}	Collector-Emitter Cutoff Current ($V_{CE} = 200\text{ V}$)	–	3.0	mAdc
V_{EBO}	Emitter-Base Reverse Voltage ($I_E = 50\text{ mA}$)	7	–	V
I_{EBO}	Emitter-Cutoff Current ($V_{EB} = 5\text{ V}$)	–	1.0	mAdc

SECOND BREAKDOWN

$I_{S/b}$	Second Breakdown Collector Current with base forward biased ($V_{CE} = 20\text{ V}$, $t = 1\text{ s}$) ($V_{CE} = 140\text{ V}$, $t = 1\text{ s}$)	12 0.15		Adc
-----------	--	------------	--	-----

ON CHARACTERISTICS (Note 2)

h_{FE}	DC Current Gain ($I_C = 10\text{ A}$, $V_{CE} = 4\text{ V}$) ($I_C = 20\text{ A}$, $V_{CE} = 4\text{ V}$)	20 10	60	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ($I_C = 10\text{ A}$, $I_B = 1\text{ A}$) ($I_C = 20\text{ A}$, $I_B = 2.5\text{ A}$)		1.0 1.5	Vdc
$V_{BE(sat)}$	Base-Emitter Saturation Voltage ($I_C = 40\text{ A}$, $I_B = 4\text{ A}$)		1.5	Vdc

DYNAMIC CHARACTERISTICS

f_T	Current Gain — Bandwidth Product ($V_{CE} = 15\text{ V}$, $I_C = 2\text{ A}$, $f = 4\text{ MHz}$)	8.0		MHz
-------	--	-----	--	-----

SWITCHING CHARACTERISTICS (Resistive Load)

t_{on}	Turn-on Time	($I_C = 20\text{ A}$, $I_{B1} = I_{B2} = 2.5\text{ A}$, $V_{CC} = 100\text{ V}$, $R_C = 5\ \Omega$)	0.8	μs
t_s	Storage Time		2.0	
t_f	Fall Time		0.35	

2. Pulse Test: Pulse Width $\leq 300\ \mu\text{s}$, Duty Cycle $\leq 2\%$.




Figure 1. Power Derating




Figure 2. Active Region Safe Operating Area




Figure 3. "On" Voltages




Figure 4. DC Current Gain




Figure 5. Resistive Switching Performance







Figure 6. Switching Times Test Circuit



SCALE 1:1

TO-204 (TO-3)
CASE 197A-05
ISSUE K

DATE 21 FEB 2000



STYLE 1:
PIN 1. BASE
2. EMITTER
CASE: COLLECTOR

STYLE 2:
PIN 1. EMITTER
2. BASE
CASE: COLLECTOR


STYLE 3:
PIN 1. GATE
2. SOURCE
CASE: DRAIN

STYLE 4:
PIN 1. ANODE = 1
2. ANODE = 2
CASE: CATHODES

- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	1.530	REF	38.86	REF
B	0.990	1.050	25.15	26.67
C	0.250	0.335	6.35	8.51
D	0.057	0.063	1.45	1.60
E	0.060	0.070	1.53	1.77
G	0.430	BSC	10.92	BSC
H	0.215	BSC	5.46	BSC
K	0.440	0.480	11.18	12.19
L	0.665	BSC	16.89	BSC
N	0.760	0.830	19.31	21.08
Q	0.151	0.165	3.84	4.19
U	1.187	BSC	30.15	BSC
V	0.131	0.188	3.33	4.77

GENERIC
MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
YY = Year
WW = Work Week

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98ASB42129B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-204 (TO-3)	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales