

**PRO PM 75W 5V 14A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

**General ordering data**

|            |                                             |
|------------|---------------------------------------------|
| Version    | Power supply, switch-mode power supply unit |
| Order No.  | <a href="#">2660200281</a>                  |
| Type       | PRO PM 75W 5V 14A                           |
| GTIN (EAN) | 4050118782028                               |
| Qty.       | 1 ST                                        |

## PRO PM 75W 5V 14A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 99 mm | Depth (inches)  | 3.8976 inch |
| Height     | 30 mm | Height (inches) | 1.1811 inch |
| Width      | 97 mm | Width (inches)  | 3.8189 inch |
| Net weight | 240 g |                 |             |

## Temperatures

|                     |                |                       |                |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -20 °C...70 °C |
| Humidity            | 5...95 % RH    |                       |                |

## Environmental Product Compliance

|                                      |                                         |
|--------------------------------------|-----------------------------------------|
| RoHS Compliance Status               | Compliant with exemption                |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl                             |
| REACH SVHC                           | Lead 7439-92-1, Lead monoxide 1317-36-8 |
| SCIP                                 | 015c3a09-4dd7-4b84-85e2-16a46fa4e79a    |

## Input

|                                                      |               |                                         |  |
|------------------------------------------------------|---------------|-----------------------------------------|--|
| Connection system                                    |               | Screw connection                        |  |
| AC input voltage range                               |               | 90...264 V AC                           |  |
| Recommended back-up fuse                             |               | 4 A at 230 V AC, characteristic curve C |  |
| Frequency range AC                                   |               | 47...63 Hz                              |  |
| Rated input voltage                                  |               | 100...240 V AC                          |  |
| AC current consumption                               |               | 1 A @ 230 V AC / 2 A @ 115 V AC         |  |
| Inrush current                                       |               | max. 45 A                               |  |
| Current consumption in relation to the input voltage | Voltage type  | AC                                      |  |
|                                                      | Input voltage | 230 V                                   |  |
|                                                      | Input current | 1 A                                     |  |
|                                                      | Voltage type  | AC                                      |  |
|                                                      | Input voltage | 115 V                                   |  |
|                                                      | Input current | 2 A                                     |  |
| Nominal power consumption                            |               | 91.5 VA                                 |  |

## Output

|                                  |                                                                       |                                |                        |
|----------------------------------|-----------------------------------------------------------------------|--------------------------------|------------------------|
| Output power                     | 75 W                                                                  | Mains failure bridge-over time | 20 ms                  |
| Connection system                | Screw connection                                                      | Rated output voltage           | 5 V DC                 |
| Residual ripple, breaking spikes | < 100 mVPP                                                            | Parallel connection option     | Yes, with diode module |
| Overload protection              | 120%...180% Inominal, hiccup mode with automatic recovery             | Surge protection               | 5.6...6.8 V @ 5 V DC   |
| Output voltage, note             | ± 10% nominal output voltage tolerance, adjustable with potentiometer | Rated current                  | 14 A                   |

## PRO PM 75W 5V 14A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## General data

|                                        |                        |                   |                   |
|----------------------------------------|------------------------|-------------------|-------------------|
| Degree of efficiency                   | 82 %                   | Humidity          | 5...95 % RH       |
| Protection degree                      | IP20                   | Status indication | LED green: ready  |
| Mounting position, installation notice | Panel mount, screw fix | Derating          | > 50°C (2% / 1°C) |
| Short-circuit protection               | Yes                    |                   |                   |

## EMC / shock / vibration

|                                    |                                                                                                                                                            |                                           |                                                                           |
|------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------|---------------------------------------------------------------------------|
| Shock resistance IEC 60068-2-27    | 30 g in all directions                                                                                                                                     | Noise emission in accordance with EN55032 | Class B                                                                   |
| Interference immunity test acc. to | Burst: EN 61000-4-4 / ESD EN 61000-4-2, EN61000-4-3 (HF field), EN 61000-4-5 (surge), EN 61000-4-6 (conducted), EN61000-4-8 (Fields), EN 61000-4-11 (Dips) | Vibration resistance IEC 60068-2-6        | 10...500 Hz, constant acceleration 5 g, 10 minutes/cycle, 60 minutes/axis |

## Insulation coordination

|                                   |        |                                  |      |
|-----------------------------------|--------|----------------------------------|------|
| Insulation voltage, input/output  | 3 kV   | Insulation voltage input / earth | 2 kV |
| Insulation voltage output / earth | 0.5 kV |                                  |      |

## Electrical safety (applied standards)

|                          |                                                        |  |  |
|--------------------------|--------------------------------------------------------|--|--|
| Safety extra-low voltage | SELV acc. to IEC 60950-1, PELV according to EN 60204-1 |  |  |
|--------------------------|--------------------------------------------------------|--|--|

## Connection data (input)

|                                           |                      |                                           |                   |
|-------------------------------------------|----------------------|-------------------------------------------|-------------------|
| Connection system                         | Screw connection     | Conductor cross-section, AWG/kcmil , max. | 12                |
| Conductor cross-section, AWG/kcmil , min. | 21                   | Conductor cross-section, rigid , max.     | 4 mm <sup>2</sup> |
| Conductor cross-section, rigid , min.     | 0.34 mm <sup>2</sup> |                                           |                   |

## Connection data (output)

|                                           |                      |                                           |                   |
|-------------------------------------------|----------------------|-------------------------------------------|-------------------|
| Connection system                         | Screw connection     | Conductor cross-section, AWG/kcmil , max. | 12                |
| Conductor cross-section, AWG/kcmil , min. | 21                   | Conductor cross-section, rigid , max.     | 4 mm <sup>2</sup> |
| Conductor cross-section, rigid , min.     | 0.34 mm <sup>2</sup> |                                           |                   |

## Signalling

|                   |                  |  |  |
|-------------------|------------------|--|--|
| Status indication | LED green: ready |  |  |
|-------------------|------------------|--|--|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002540    | ETIM 7.0    | EC002540    |
| ETIM 8.0    | EC002540    | ETIM 9.0    | EC002540    |
| ETIM 10.0   | EC002540    | ECLASS 9.0  | 27-04-07-01 |
| ECLASS 9.1  | 27-04-07-01 | ECLASS 10.0 | 27-04-07-01 |
| ECLASS 11.0 | 27-04-07-01 | ECLASS 12.0 | 27-04-07-01 |
| ECLASS 13.0 | 27-04-07-01 | ECLASS 14.0 | 27-04-07-01 |
| ECLASS 15.0 | 27-04-07-01 |             |             |