WIMA MKP-X2

Metallized Polypropylene (PP) RFI-Capacitors Class X2 in PCM 7.5 mm to 37.5 mm. Capacitances from 1000 pF to 10 µF. Rated Voltage 305 VAC.

Special Features

- **Reliable self-healing**
- **High degree of interference suppression due to good attenuation and low ESR**
- **AEC-Q200 qualified** AEC-Q200
- **According to RoHS 2015/863/EU**


Typical Applications

Class X2 RFI applications to meet EMC regulations

- **Capacitors connected to the mains between phase and neutral or phase conductors**
- **General requirements, pulse peak voltage ⩽ 2.5 kV**

Construction

Dielectric:
Polypropylene (PP) film
Capacitor electrodes:
Vacuum-deposited
Internal construction:



Encapsulation:
Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0
Terminations:
Tinned wire.
Marking:
Colour: Red. Marking: Black.

Electrical Data

Capacitance range: 1000 pF to 10 µF
Rated voltage: 305 VAC
Continuous DC voltage* (general guide): ⩽ 560 V
Capacitance tolerances:
±20%, ±10%, ±5%
Operating temperature range:
–55° C to +105° C
Climatic test category:
55/105/56 in accordance with IEC
Passive flammability class:
B for capacitors with V > 1750 mm³
C for capacitors with V ⩽ 1750 mm³
Test specifications:
In accordance with IEC 60384-14
Dissipation factors at + 20° C: tan δ

at f	C ⩽ 0.1 µF	0.1 µF < C ⩽ 1.0 µF	C > 1.0 µF
1 kHz	⩽ 18 x 10^{-4}	⩽ 20 x 10^{-4}	⩽ 20 x 10^{-4}
10 kHz	⩽ 20 x 10^{-4}	⩽ 60 x 10^{-4}	–
100 kHz	⩽ 50 x 10^{-4}	–	–

Insulation resistance at +20° C:
C ⩽ 0.33 µF: ⩾ 1.5 x 10^4 MΩ
C > 0.33 µF: ⩾ 5000 sec (MΩ x µF)
Measuring voltage: 100 V/1 min.
Maximum pulse rise time:
100 V/µsec for pulses equal to a voltage amplitude with $\sqrt{2}$ x 305 VAC = 432 V according to IEC 60384-14
Test voltage:
C ⩽ 1.0 µF: 2260 VDC, 2 sec.
C > 1.0 µF: 1800 VDC, 2 sec.
Reliability:
Operational life > 300 000 hours
Failure rate < 2 fit (0.5 x U_r and 40° C)

Approvals:

Country	Authority	Specification	Symbol	Approval-No.
Germany	VDE	IEC 60384-14/4		40003472
USA/Canada	UL	UL 60384-14 CAN/CSA-E60384-14		E 134915
China	CQC	CQC11-471115-2016		CQC20001271097

Mechanical Tests

Pull test on pins: 10 N in direction of pins according to IEC 60068-2-21
Vibration: 6 hours at 10 ... 2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6
Low air density: 1kPa = 10 mbar in accordance with IEC 60068-2-13
Bump test: 4000 bumps at 390 m/sec² in accordance with IEC 60068-2-29

* If safety-approved EMI suppression capacitors are operated with a DC voltage being above the specified AC voltage rating the given approvals are no longer valid (IEC 60384-14).

Furthermore the permissible pulse rise time du/dt ($F_{max.}$) will be subject to a reduction according to

$F_{max.} = F_r \times \sqrt{2} \times UAC/UDC$

if the DC operating voltage UDC is higher than $\sqrt{2}$ x UAC

Packing

Available taped and reeled up to and including case size 15 x 26 x 31.5 / PCM 27.5 mm.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data


Capacitance	305 VAC* W	H	L	PCM**	Part number
1000 pF	4	9	10	7.5	MKX2AW11002C00____
1200 „	4	9	10	7.5	MKX2AW11202C00____
1500 „	4	9	10	7.5	MKX2AW11502C00____
1800 „	4	9	10	7.5	MKX2AW11802C00____
2200 „	4	9	10	7.5	MKX2AW12202C00____
2700 „	4	9	10	7.5	MKX2AW12702C00____
3300 „	4	9	10	7.5	MKX2AW13302C00____
3900 „	4	9	10	7.5	MKX2AW13902C00____
4700 „	4	9	10	7.5	MKX2AW14702C00____
5600 „	4	9	10	7.5	MKX2AW15602C00____
6800 „	4	9	10	7.5	MKX2AW16802C00____
8200 „	4	9	10	7.5	MKX2AW18202C00____
0.01 µF	4	9	10	7.5	MKX2AW21002C00____
	5	11	13	10	MKX2AW21003F00____
0.012 „	4	9	10	7.5	MKX2AW21202C00____
	5	11	13	10	MKX2AW21203F00____
0.015 „	4	9	10	7.5	MKX2AW21502C00____
	5	11	13	10	MKX2AW21503F00____
0.018 „	4	9	10	7.5	MKX2AW21802C00____
	5	11	13	10	MKX2AW21803F00____
0.022 „	4	9	10	7.5	MKX2AW22202C00____
	5	11	13	10	MKX2AW22203F00____
0.027 „	5	10.5	10.3	7.5	MKX2AW22702E00____
	5	11	13	10	MKX2AW22703F00____
0.033 „	5	10.5	10.3	7.5	MKX2AW23302E00____
	5	11	13	10	MKX2AW23303F00____
0.039 „	5.7	12.5	10.3	7.5	MKX2AW23902F00____
	5	11	13	10	MKX2AW23903F00____
0.047 „	5.7	12.5	10.3	7.5	MKX2AW24702F00____
	6	12.5	13	10	MKX2AW24703H00____
	5	11	18	15	MKX2AW24704B00____
0.056 „	6	12.5	13	10	MKX2AW25603H00____
	5	11	18	15	MKX2AW25604B00____
0.068 „	6	12.5	13	10	MKX2AW26803H00____
	5	11	18	15	MKX2AW26804B00____
0.082 „	6	12.5	13	10	MKX2AW28203H00____
	5	11	18	15	MKX2AW28204B00____

* f = 50/60 Hz

** PCM = Printed circuit module = pin spacing

Dims. in mm.

d = 0.6 Ø if PCM < 15
d = 0.8 Ø if PCM ⩾ 15



Part number completion:	
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD

Taped version see page 151.

Rights reserved to amend design data without prior notification.

Continuation page 86

Continuation


General Data

Capacitance	305 VAC* W	H	L	PCM**	Part number
0.1 µF	8	12	13	10	MKX2AW31003I00____
	5	11	18	15	MKX2AW31004B00____
	6	12.5	18	15	MKX2AW31004C00____
0.12 „	6	12.5	18	15	MKX2AW31204C00____
0.15 „	6	12.5	18	15	MKX2AW31504C00____
	8	15	18	15	MKX2AW31504F00____
	6	15	26.5	22.5	MKX2AW31505B00____
0.18 „	8	15	18	15	MKX2AW31804F00____
	6	15	26.5	22.5	MKX2AW31805B00____
0.22 „	9	14	18	15	MKX2AW32204H00____
	8	15	18	15	MKX2AW32204F00____
	6	15	26.5	22.5	MKX2AW32205B00____
0.27 „	8	15	18	15	MKX2AW32704F00____
	7	16.5	26.5	22.5	MKX2AW32705D00____
0.33 „	11	14	18	15	MKX2AW33304M00____
	9	16	18	15	MKX2AW33304J00____
	7	16.5	26.5	22.5	MKX2AW33305D00____
0.39 „	8.5	18.5	26.5	22.5	MKX2AW33905F00____
0.47 „	8.5	18.5	26.5	22.5	MKX2AW34705F00____
	10.5	19	26.5	22.5	MKX2AW34705G00____
	9	19	31.5	27.5	MKX2AW34706A00____
0.56 „	10.5	19	26.5	22.5	MKX2AW35605G00____
	9	19	31.5	27.5	MKX2AW35606A00____
0.68 „	10.5	19	26.5	22.5	MKX2AW36805G00____
	11	21	26.5	22.5	MKX2AW36805I00____
	9	19	31.5	27.5	MKX2AW36806A00____
0.82 „	11	21	26.5	22.5	MKX2AW38205I00____
	9	19	31.5	27.5	MKX2AW38206A00____

* f = 50/60 Hz


** PCM = Printed circuit module = pin spacing

Dims. in mm.



d = 0.6 Ø if PCM = 10
d = 0.8 Ø if PCM ⩾ 15

Part number completion:	
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 151.	



Impedance change with frequency (general guide).

Rights reserved to amend design data without prior notification.

Continuation page 87

Continuation

General Data


Capacitance	305 VAC* W	H	L	PCM**	Part number
1.0 µF	11	21	26.5	22.5	MKX2AW41005I00____
	11	21	31.5	27.5	MKX2AW41006B00____
	13	24	31.5	27.5	MKX2AW41006D00____
1.2 „	11	21	31.5	27.5	MKX2AW41206B00____
1.5 „	13	24	31.5	27.5	MKX2AW41506D00____
	15	26	31.5	27.5	MKX2AW41506F00____
	13	24	41.5	37.5	MKX2AW41507C00____
1.8 „	13	24	31.5	27.5	MKX2AW41806D00____
	13	24	41.5	37.5	MKX2AW41807C00____
2.2 „	15	26	31.5	27.5	MKX2AW42206F00____
	17	29	31.5	27.5	MKX2AW42206G00____
	13	24	41.5	37.5	MKX2AW42207C00____
	15	26	41.5	37.5	MKX2AW42207D00____
2.7 „	17	29	31.5	27.5	MKX2AW42706G00____
	15	26	41.5	37.5	MKX2AW42707D00____
	17	29	41.5	37.5	MKX2AW42707E00____
3.3 „	17	34.5	31.5	27.5	MKX2AW43306I00____
	20	39.5	31.5	27.5	MKX2AW43306J00____
	15	26	41.5	37.5	MKX2AW43307D00____
	17	29	41.5	37.5	MKX2AW43307E00____
3.9 „	17	34.5	31.5	27.5	MKX2AW43906I00____
	17	29	41.5	37.5	MKX2AW43907E00____
	19	32	41.5	37.5	MKX2AW43907F00____
4.7 „	20	39.5	31.5	27.5	MKX2AW44706J00____
	19	32	41.5	37.5	MKX2AW44707F00____
	20	39.5	41.5	37.5	MKX2AW44707G00____
5.6 „	19	32	41.5	37.5	MKX2AW45607F00____
	20	39.5	41.5	37.5	MKX2AW45607G00____
6.8 „	20	39.5	41.5	37.5	MKX2AW46807G00____
	24	45.5	41.5	37.5	MKX2AW46807H00____
8.2 „	24	45.5	41.5	37.5	MKX2AW48207H00____
	31	46	41.5	37.5	MKX2AW48207I00____
10 µF	24	45.5	41.5	37.5	MKX2AW51007H00____
	31	46	41.5	37.5	MKX2AW51007I00____

* f = 50/60 Hz

** PCM = Printed circuit module = pin spacing

Dims. in mm.

d = 0.8 Ø if PCM ⩽ 27.5
d = 1.0 Ø if PCM = 37.5



Part number completion:	
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD

Taped version see page 151.


Rights reserved to amend design data without prior notification.

Continuation page 88

WIMA MKP-X2


Continuation

Permissible AC current in relation to frequency at 10° C internal temperature rise (general guide).



WIMA MKP-Y2

Permissible AC current in relation to frequency at 10° C internal temperature rise (general guide).



Technical information and general data see page 89

Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{max.} \leqslant 125°$ C
soldering: $T_{max.} \leqslant 135°$ C


Polypropylene: preheating: $T_{max.} \leqslant 100°$ C
soldering: $T_{max.} \leqslant 110°$ C

Single wave soldering
Soldering bath temperature: $T < 260°$ C
Dwell time: $t < 5$ sec

Double wave soldering
Soldering bath temperature: $T < 260°$ C
Dwell time: $\sum t < 5$ sec

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.

Wave soldering



Typical temperature/time graph for double wave soldering

WIMA Quality and Environmental Philosophy

ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- **incoming material inspection**
- **metallization**
- **film inspection**
- **schoopage**
- **pre-healing**
- **pin attachment**
- **cast resin preparation/encapsulation**
- **100% final inspection**
- **Testing as per customer requirements**

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- **Lead**
- **PCB**
- **CFC**
- **Hydrocarbon chloride**
- **Chromium 6+**
- **PBB/PBDE**
- **Arsenic**
- **Cadmium**
- **Mercury**
- **etc.**

We merely use pure, recyclable materials for packing our components, such as:

- **carton**
- **cardboard**
- **adhesive tape made of paper**
- **polystyrene**

We almost completely refrain from using packing materials such as:

- **adhesive tapes made of plastic**
- **metal clips**

RoHS Compliance

According to the RoHS Directive 2015/863/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has re-fraind from using such substances since years already.

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

05.25

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm




Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm
*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	**PCM 5 taping**	**PCM 7.5 taping**	**PCM 10 taping***	**PCM 15 taping***	**PCM 22.5 taping**	**PCM 27.5 taping**
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W_0	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W_1	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W_2	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D_0	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	*38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P_0	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P_1	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P_2	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H ▲	16.5 ±0.3	16.5 ±0.3	16.5 ±0.5	16.5 ±0.5	16.5 ±0.5	16.5 ±0.5	16.5 ±0.5
		18.5 ±0.5	18.5 ±0.5	18.5 ±0.5	18.5 ±0.5	18.5 ±0.5	18.5 ±0.5	18.5 ±0.5
Feed hole centre to top edge of the component	H_1	$H+H_{component} < H_1$ 32.25 max.	$H+H_{component} < H_1$ 32.25 max.	$H+H_{component} < H_1$ 24.5 to 31.5	$H+H_{component} < H_1$ 25.0 to 31.5	$H+H_{component} < H_1$ 26.0 to 37.0	$H+H_{component} < H_1$ 30.0 to 43.0	$H+H_{component} < H_1$ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 $^{+0.8}_{-0.2}$	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	•0.5 ±0.05 or $0.6^{+0.06}_{-0.05}$	•0.5 ±0.05 or $0.6^{+0.06}_{-0.05}$	$0.8^{+0.08}_{-0.05}$	$0.8^{+0.08}_{-0.05}$	$0.8^{+0.08}_{-0.05}$
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 152)	▲	ROLL/AMMO		AMMO				
		REEL Ø 360 max. Ø 30 ±1 B 52 ±2 / 58 ±2 depending on comp. dimensions		REEL Ø 360 max. Ø 30 ±1 B 52 ±2 / 58 ±2 / 66 ±2 or REEL Ø 500 max. Ø 25 ±1 B 54 ±2 / 60 ±2 / 68 ±2 depending on PCM and component dimensions				
Unit		see details page 153.						

▲ When ordering please specify dimension H and required packaging type.

• Diameter of pins see General Data.


* PCM 10 and PCM 15 can be crimped to PCM 7.5.
Position of components according to PCM 7.5 (sketch 1). P_0 = 12.7 or 15.0 is possible

Dims in mm.


Please clarify customer-specific deviations with the manufacturer.

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


ROLL Packaging



AMMO Packaging



REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

- WIMA supplier number
- Date code
- Customer's P/O number
- P/O line
- Customer's part number
- WIMA part number
- Quantity
- WIMA confirmation number
- Country of origin
- Customer name
- Handling unit number
- Week of delivery.

In addition part description of

– article
– capacitance value
– rated voltage
– dimensions
– technical note
– capacitance tolerance
– packing
– connecting information



BARCODE PDF417
BARCODE 2D Datamatrix

Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 27.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
								Ø 360		Ø 500		340 x 340		490 x 370	
						H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
	W	H	L	Codes	S	N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	**0B**	5000	2200		2500		–		2800		–	
	3	7.5	4.6	**0C**	5000	2000		2300		–		2300		–	
	3.8	8.5	4.6	**0D**	5000	1500		1800		–		1800		–	
	4.6	9	4.6	**0E**	5000	1200		1500		–		1500		–	
	5.5	10	4.6	**0F**	5000	900		1200		–		1200		–	
5 mm	2.5	6.5	7.2	**1A**	5000	2200		2500		–		2800		–	
	3	7.5	7.2	**1B**	5000	2000		2300		–		2300		–	
	3.5	8.5	7.2	**1C**	5000	1600		2000		–		2000		–	
	4.5	6	7.2	**1D**	6000	1300		1500		–		1500		–	
	4.5	9.5	7.2	**1E**	4000	1300		1500		–		1500		–	
	5	10	7.2	**1F**	3500	1100		1400		–		1400		–	
	5.5	7	7.2	**1G**	4000	1000		1200		–		1200		–	
	5.5	11.5	7.2	**1H**	2500	1000		1200		–		1200		–	
	6.5	8	7.2	**1I**	2500	800		1000		–		1000		–	
	7.2	8.5	7.2	**1J**	2500	700		1000		–		1000		–	
	7.2	13	7.2	**1K**	2000	700		950		–		1000		–	
	8.5	10	7.2	**1L**	2000	600		800		–		800		–	
	8.5	14	7.2	**1M**	1500	600		800		–		800		–	
	11	16	7.2	**1N**	1000	500		600		–		640		–	
7.5 mm	2.5	7	10	**2A**	5000	–		2500		4400		2500		–	
	3	8.5	10	**2B**	5000	–		2200		4300		2300		4150	
	4	9	10	**2C**	4000	–		1700		3200		1700		3000	
	4.5	9.5	10.3	**2D**	3500	–		1500		2900		1400		2700	
	5	10.5	10.3	**2E**	3000	–		1300		2500		1300		–	
	5.7	12.5	10.3	**2F**	2000	–		1000		2200		1100		–	
	7.2	12.5	10.3	**2G**	1500	–		900		1800		1000		–	
10 mm	3	9	13	**3A**	3000	–		1100		2200		–		1900	
	4	9	13	**3C**	3000	–		900		1600		–		1450	
	4	9.5	13	**3D**	3000	–		900		1600		–		1400	
	5	11	13	**3F**	3000	–		700		1300		–		1100	
	6	12	13	**3G**	2400	–		550		1100		–		1000	
	6	12.5	13	**3H**	2400	–		550		1100		–		1000	
	8	12	13	**3I**	2000	–		400		800		–		740	
15 mm	5	11	18	**4B**	2400	–		600		1200		–		1150	
	6	12.5	18	**4C**	2000	–		500		1000		–		1000	
	7	14	18	**4D**	1600	–		450		900		–		850	
	8	15	18	**4F**	1200	–		400		800		–		740	
	9	14	18	**4H**	1200	–		350		700		–		650	
	9	16	18	**4J**	900	–		350		700		–		650	
	11	14	18	**4M**	1000	–		300		600		–		540	
22.5 mm	5	14	26.5	**5A**	1200	–		–		800		–		770	
	6	15	26.5	**5B**	1000	–		–		700		–		640	
	7	16.5	26.5	**5D**	760	–		–		600		–		550	
	8.5	18.5	26.5	**5F**	500	–		–		480		–		450	
	10.5	19	26.5	**5G**	594*	–		–		400		–		360	
	10.5	20.5	26.5	**5H**	594*	–		–		400		–		360	
	11	21	26.5	**5I**	561*	–		–		380		–		350	
27.5 mm	9	19	31.5	**6A**	567*	–		–		460/340*		–		–	
	11	21	31.5	**6B**	459*	–		–		380/280*		–		–	
	13	24	31.5	**6D**	378*	–		–		300		–		–	
	15	26	31.5	**6F**	324*	–		–		270		–		–	
	17	29	31.5	**6G**	198*	–		–		–		–		–	
	17	34.5	31.5	**6I**	198*	–		–		–		–		–	
	20	39.5	31.5	**6J**	162*	–		–		–		–		–	

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

Rights reserved to amend design data without prior notification.

Packing Quantities for Capacitors with Radial Pins in PCM 37.5 mm to 52.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
								∅ 360		∅ 500		340 x 340		490 x 370	
						H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
	W	H	L	Codes	S	N	O	F	I	H	J	A	C	B	D
37.5 mm**	9	19	41.5	**7A**	441*	–		–		–		–		–	
	11	22	41.5	**7B**	357*	–		–		–		–		–	
	13	24	41.5	**7C**	294*	–		–		–		–		–	
	15	26	41.5	**7D**	252*	–		–		–		–		–	
	17	29	41.5	**7E**	154*	–		–		–		–		–	
	19	32	41.5	**7F**	140*	–		–		–		–		–	
	20	39.5	41.5	**7G**	126*	–		–		–		–		–	
	24	45.5	41.5	**7H**	112*	–		–		–		–		–	
	28	38	41.5	**7L**	84*	–		–		–		–		–	
	31	46	41.5	**7I**	84*	–		–		–		–		–	
	35	50	41.5	**7J**	35*	–		–		–		–		–	
	40	55	41.5	**7K**	28*	–		–		–		–		–	
48.5 mm**	19	31	56	**8D**	120*	–		–		–		–		–	
	23	34	56	**8E**	80*	–		–		–		–		–	
	27	37.5	56	**8H**	84*	–		–		–		–		–	
	33	48	56	**8J**	25*	–		–		–		–		–	
	37	54	56	**8L**	25*	–		–		–		–		–	
52.5 mm	25	45	57	**9D**	70*	–		–		–		–		–	
	30	45	57	**9E**	60*	–		–		–		–		–	
	35	50	57	**9F**	25*	–		–		–		–		–	
	45	55	57	**9H**	20*	–		–		–		–		–	
	45	65	57	**9J**	20*	–		–		–		–		–	

* TPS (Tray-Packing-System). Plate versions may have different packing units.
**For Snubber capacitors in 2-pin version the PCM is changing to 38.5 respective 49.5 mm.
Samples and pre-production needs on request.

Rights reserved to amend design data without prior notification.

Updated data on www.wima.com

WIMA Part Number System

A WIMA part number consists of 18 digits and is composed as follows:

Field 1 - 4: Type description
Field 5 - 6: Rated voltage
Field 7 - 10: Capacitance
Field 11 - 12: Size and PCM
Field 13 - 14: Version code (e.g. Snubber versions)
Field 15: Capacitance tolerance
Field 16: Packing
Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	**K**	**S**	**2**	**C**	**0**	**2**	**1**	**0**	**0**	**1**	**A**	**0**	**0**	**M**	**S**	**S**	**D**
MKS 2				63 VDC		0.01 µF				2.5x6.5x7.2		-		20%	bulk	6 -2	

Type description:

SMD-PET	= SMDT
SMD-PPS	= SMDI
FKP 02	= FKP0
MKS 02	= MKS0
FKS 2	= FKS2
FKP 2	= FKP2
FKS 3	= FKS3
FKP 3	= FKP 3
MKS 2	= MKS2
MKP 2	= MKP2
MKS 4	= MKS4
MKP 4	= MKP4
MKP 10	= MKP1
FKP 4	= FKP4
FKP 1	= FKP1
MKP-X2	= MKX2
MKP-X1 R	= MKX1
MKP-Y2	= MKY2
MKP 4F	= MKPF
Snubber MKP	= SNMP
Snubber FKP	= SNFP
GTO MKP	= GTOM
DC-LINK MKP 4	= DCP4
DC-LINK MKP 6	= DCP6
DC-LINK HC	= DCHC

Rated voltage:

50 VDC	= B0
63 VDC	= C0
100 VDC	= D0
250 VDC	= F0
400 VDC	= G0
450 VDC	= H0
520 VDC	= H2
600 VDC	= I0
630 VDC	= J0
700 VDC	= K0
800 VDC	= L0
850 VDC	= M0
900 VDC	= N0
1000 VDC	= O1
1100 VDC	= P0
1200 VDC	= Q0
1250 VDC	= R0
1500 VDC	= S0
1600 VDC	= T0
1700 VDC	= TA
2000 VDC	= U0
2500 VDC	= V0
3000 VDC	= W0
4000 VDC	= X0
6000 VDC	= Y0
230 VAC	= 3Y
275 VAC	= 1W
300 VAC	= 2W
305 VAC	= AW
350 VAC	= BW
440 VAC	= 4W
...	

Capacitance:

22 pF	= 0022
47 pF	= 0047
100 pF	= 0100
150 pF	= 0150
220 pF	= 0220
330 pF	= 0330
470 pF	= 0470
680 pF	= 0680
1000 pF	= 1100
1500 pF	= 1150
2200 pF	= 1220
3300 pF	= 1330
4700 pF	= 1470
6800 pF	= 1680
0.01 µF	= 2100
0.022 µF	= 2220
0.047 µF	= 2470
0.1 µF	= 3100
0.22 µF	= 3220
0.47 µF	= 3470
1 µF	= 4100
2.2 µF	= 4220
4.7 µF	= 4470
10 µF	= 5100
22 µF	= 5220
47 µF	= 5470
100 µF	= 6100
220 µF	= 6220
1000 µF	= 7100
1500 µF	= 7150
...	

Size:

4.8x3.3x3 Size 1812	= KA
4.8x3.3x4 Size 1812	= KB
5.7x5.1x3.5 Size 2220	= QA
5.7x5.1x4.5 Size 2220	= QB
7.2x6.1x3 Size 2824	= TA
7.2x6.1x5 Size 2824	= TB
10.2x7.6x5 Size 4030	= VA
12.7x10.2x6 Size 5040	= XA
15.3x13.7x7 Size 6054	= YA
2.5x7x4.6 PCM 2.5	= 0B
3x7.5x4.6 PCM 2.5	= 0C
2.5x6.5x7.2 PCM 5	= 1A
3x7.5x7.2 PCM 5	= 1B
2.5x7x10 PCM 7.5	= 2A
3x8.5x10 PCM 7.5	= 2B
3x9x13 PCM 10	= 3A
4x9x13 PCM 10	= 3C
5x11x18 PCM 15	= 4B
6x12.5x18 PCM 15	= 4C
5x14x26.5 PCM 22.5	= 5A
6x15x26.5 PCM 22.5	= 5B
9x19x31.5 PCM 27.5	= 6A
11x21x31.5 PCM 27.5	= 6B
9x19x41.5 PCM 37.5	= 7A
11x22x41.5 PCM 37.5	= 7B
19x31x56 PCM 48.5	= 8D
25x45x57 PCM 52.5	= 9D
...	

Version code:

Standard	= 00
Version A1	= 1A
Version A1.1.1	= 1B
Version A2	= 2A
...	

Tolerance:

±20%	= M
±10%	= K
±5%	= J
±2.5%	= H
±1%	= E
...	

Packing:

AMMO H16.5 340x340	= A
AMMO H16.5 490x370	= B
AMMO H18.5 340x340	= C
AMMO H18.5 490x370	= D
REEL H16.5 360	= F
REEL H16.5 500	= H
REEL H18.5 360	= I
REEL H18.5 500	= J
ROLL H16.5	= N
ROLL H18.5	= O
BLISTER W12 180	= P
BLISTER W12 330	= Q
BLISTER W16 330	= R
BLISTER W24 330	= T
Bulk/TPS Standard	= S
...	

Pin length (untaped)

3.5 ±0.5	= C9
6 -2	= SD
16 ±1	= P1
...	

Pin length (taped)

none	= 00

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.