



Data Sheet | Item Number: 221-2401

Inline splicing connector with levers; for all conductor types; max. 4 mm²; 2-conductor;
transparent housing; white cover; Surrounding air temperature: max 85°C (T85); 4,00
mm²; transparent

<https://www.wago.com/221-2401>



Color: ☐ transparent



Inline splicing connector with levers, 221 Series, CAGE CLAMP®

Enjoy error-free electrical installations with inline splicing connector with levers (item number 221-2401). From intercom system wiring to electric ovens—connecting various conductor types is quick and hassle-free with WAGO's compact 221 Series splicing connector. Strip lengths must be 11 mm when connecting conductors to inline splicing connector with levers. Rated current and voltage are key factors to consider when selecting a splicing connector, as they determine the product's suitability for different applications. This product has a rated voltage of 450 V and a rated current of 32 A, making it suitable for high-load applica-

tions. This product features conductor terminals and utilizes CAGE CLAMP®. Our reliable and maintenance-free CAGE CLAMP® connection makes it easy to connect all conductor types without having to prepare the conductor. For example, you don't need to crimp ferrules. The item's dimensions are (8.1 x 8.9 x 35.5) mm (width x height x depth). Inline splicing connector with levers is suitable for conductor cross sections ranging from 0.2 mm² to 4 mm².

WAGO's 221 Series Splicing Connector with levers impresses with its innovative design for different conductor cross-sections. That's why WAGO's lever-equipped splicing connector holds a unique trademark within electrical interconnection technology. The flat levers, which fit seamlessly into the 221's base, act like a cast when closed and can be positioned neatly in any housing without disturbing edges. Due to the wide design of each lever, they can all be operated perfectly without tools for convenient conductor terminations. The transparent housing displays robust technology and enables immediate visual inspection for the correct contact of solid, stranded and fine-stranded conductors. Resembling piano keys, the levers' design perfectly combines the functional and aesthetic connection technology "Made by WAGO."

Notes

General safety information

NOTICE: Observe installation and safety instructions!

- **Only to be used by electricians!**
- Do not work under voltage/load!
- Use only for proper use!
- Observe national regulations/standards/guidelines!
- Observe technical specifications for the products!
- Observe the number of permissible potentials!
- Do not use damaged/dirty components!
- Observe conductor types, cross-sections and strip lengths!
- Insert conductor until it hits the product's backstop!
- Use original accessories!

To be sold only with installation instructions!

Electrical data				
Ratings per		EN 60664		
Overvoltage category	III	III	II	
Pollution degree	3	2	2	
Nominal voltage	-	-	450 V	
Rated impulse withstand voltage	-	-	4 kV	
Rated current	-	-	32 A	

Ratings per UL	
Rated voltage UL (Use Group C)	600 V
Rated current UL (Use Group C)	20 A

Connection Data		
Clamping units	2	Connection 1 Connection technology CAGE CLAMP® Actuation type Lever Connectable conductor materials Copper Nominal cross-section 4 mm² / 12 AWG Solid conductor 0.2 ... 4 mm² / 20 ... 12 AWG Stranded conductor 0.2 ... 2.5 mm² / 18 ... 12 AWG Fine-stranded conductor 0.34 ... 4 mm² / 18 ... 12 AWG Strip length 11 mm / 0.43 inches
Total number of potentials	1	

Physical data		
Width	8.1 mm / 0.319 inches	
Height	8.9 mm / 0.35 inches	
Depth	35.5 mm / 1.398 inches	

Material data		
Note (material data)	Information on material specifications can be found here	
Color	transparent	
Cover color	white	
Material group	IIIa	
Insulation material (main housing)	Polycarbonate (PC)	
Flammability class per UL94	V2	
Fire load	0.039 MJ	
Actuator color	orange	
Weight of insulation material	0.84 g	
Weight	2.4 g	

Environmental requirements		
Continuous operating temperature	-60 ... +105 °C	

Commercial data		
PU (SPU)	600 (60) pcs	
Packaging type	Box	
Country of origin	CH	
GTIN	4066966120271	
Customs tariff number	85369010000	

Product Classification		
UNSPSC	39121409	
ETIM 9.0	EC000446	
ETIM 10.0	EC000446	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant, No Exemption	

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60998	NTR NL-7990	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
cULus_Listed_667F Underwriters Laboratories Inc.	UL 486C	E69654	UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-
ENE 05 DEKRA Certification B.V.	EN 60998	71-168264			
UL Underwriters Laboratories Inc.	UL 467	E201573			



Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	EN 60998	23-2417173-PDA
LR Lloyds Register	EN 60998	LR2446364TA
PRS Polski Rejestr Statków	EN 60998	TE/1093/880590/23

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 221-2401



CAD/CAE-Data

CAD data
2D/3D Models 221-2401



CAE data
EPLAN Data Portal 221-2401
ZUKEN Portal 221-2401



1 Compatible Products

1.1 Optional Accessories

1.1.1 General accessories

1.1.1.1 Moisture protection



Item No.: 207-1372
Gelbox; inline connection; for cables; with gel; 221 Series; max. 4 mm² connectors; without splicing connectors; Size 1; gray



Item No.: 207-1373
Gelbox; inline connection; for cables; with gel; 221 Series; max. 4 mm² connectors; without splicing connectors; Size 2; gray



Item No.: 207-1375
Gelbox; inline connection; for cables; with gel; 221 Series; max. 4 mm² connectors; without splicing connectors; Size 3; gray

1.1.2 Installation

1.1.2.1 Mounting accessories



Item No.: 221-2501
Mounting carrier with strain relief; 1-way; for inline splicing connector with lever; for screw mounting; gray



Item No.: 221-2511
Mounting carrier with strain relief; 1-way; for inline splicing connector with lever; with snap-in mounting foot; gray



Item No.: 221-2502
Mounting carrier with strain relief; 2-way; for inline splicing connector with lever; for screw mounting; gray



Item No.: 221-2512
Mounting carrier with strain relief; 2-way; for inline splicing connector with lever; with snap-in mounting foot; gray

1.1.2.1 Mounting accessories

 Item No.: 221-2503 Mounting carrier with strain relief; 3-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2513 Mounting carrier with strain relief; 3-way; for inline splicing connector with lever; with snap-in mounting foot; gray	 Item No.: 221-2504 Mounting carrier with strain relief; 4-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2514 Mounting carrier with strain relief; 4-way; for inline splicing connector with lever; with snap-in mounting foot; gray
 Item No.: 221-2505 Mounting carrier with strain relief; 5-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2515 Mounting carrier with strain relief; 5-way; for inline splicing connector with lever; with snap-in mounting foot; gray	 Item No.: 221-2521 Mounting carrier; 1-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2531 Mounting carrier; 1-way; for inline splicing connector with lever; with snap-in mounting foot; gray
 Item No.: 221-2522 Mounting carrier; 2-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2532 Mounting carrier; 2-way; for inline splicing connector with lever; with snap-in mounting foot; gray	 Item No.: 221-2523 Mounting carrier; 3-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2533 Mounting carrier; 3-way; for inline splicing connector with lever; with snap-in mounting foot; gray
 Item No.: 221-2524 Mounting carrier; 4-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2534 Mounting carrier; 4-way; for inline splicing connector with lever; with snap-in mounting foot; gray	 Item No.: 221-2525 Mounting carrier; 5-way; for inline splicing connector with lever; for screw mounting; gray	 Item No.: 221-2535 Mounting carrier; 5-way; for inline splicing connector with lever; with snap-in mounting foot; gray
 Item No.: 209-123 Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide; gray	 Item No.: 209-1116 Mounting foot with screw; for DIN-15 rail; can be screwed on terminal blocks with fixing flange; 6.5 mm wide; gray	 Item No.: 209-120 Mounting foot; can be snapped on terminal blocks with snap-in mounting foot; for mounting on relay-modules; 6.4 mm wide; gray	 Item No.: 209-1115 Mounting foot; for DIN-15 rail; can be snapped on terminal blocks with snap-in mounting foot; 6.5 mm wide; gray

1.1.3 Marking


1.1.3.1 Marking strip



Item No.: 210-834
Marking strips; on reel; 5 mm wide; plain; Self-adhesive; white

Installation Notes

Conductor termination





Push up the lever to open the clamping unit and insert the conductor.



Push the lever back down.


Installation




Place the inline splicing connector on the carrier in front of the mounting position.

Push the connector to the center position until it snaps into place.


Application



Perfect for test setups



Simple extension of lines



Lighting connection in suspended ceilings



Multi-pole, fixed lighting fixture wiring