


**MPX1D1235LR15**

Aliases (UPI2X11235LR15)

KEMET, MPX, Metal Composite, 20%, 150 nH, 1235(5350)



Click [here](#) for the 3D model.

**Dimensions**

|           |                 |
|-----------|-----------------|
| Chip Size | 1235(5350)      |
| L         | 13.2mm +/-0.4mm |
| W         | 12.5mm +/-0.2mm |
| T         | 3.5mm MAX       |
| G         | 4.7mm +/-0.3mm  |

**Packaging Specifications**

|                          |            |
|--------------------------|------------|
| Typical Component Weight | 2.9 g      |
| Packaging                | T&R, 330mm |
| Packaging Quantity       | 500        |

**General Information**

|               |                              |
|---------------|------------------------------|
| Series        | MPX                          |
| Style         | SMD Molded                   |
| Core          | Metal Composite              |
| Description   | Surface Mount Inductor       |
| Features      | Power Inductors              |
| RoHS          | Yes                          |
| Miscellaneous | 40 (K) Temperature Rise Max. |

**Specifications**

|                         |                                                                                                                   |
|-------------------------|-------------------------------------------------------------------------------------------------------------------|
| Inductance              | 150 nH                                                                                                            |
| Inductance Tolerance    | 20%                                                                                                               |
| Temperature Range       | -55/+155°C                                                                                                        |
| Shielded                | Yes                                                                                                               |
| Current                 | 39.9 A (Irms, 40C Rise By Self Heating), 54 A (Isat, 20% Drop In Inductance), 85 A (Isat, 30% Drop In Inductance) |
| DC Resistance           | 1.3 mOhms                                                                                                         |
| Self-Resonant Frequency | 128 MHz                                                                                                           |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.