

# Antenna Cable FAKRA C plug to MHF® I plug 1.13 - 20 cm 2 prepunched hole

## Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



**Item no. 90731**

EAN: 4043619907311

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x FAKRA C plug
  - 1 x MHF® I plug
- FAKRA D: RAL 4004 Claret violet
- Impedance: 50 Ohm
- Cable type: 1.13
- Cable type: coaxial
- Cable diameter: ca. 1.13 mm
- Cable attenuation: 3.2 dB @ 2.4 GHz per meter
- Smallest bending radius: 4.5 mm
- Mounting plate: steel
- 2 prepunched holes for mounting
- Thread type: M3
- Cable length without connectors: ca. 20 cm
- Dimensions (LxWxH): ca. 24 x 12 x 9 mm

## Package content

- Antenna cable

## Images



## Interface

|              |                             |
|--------------|-----------------------------|
| Connector 1: | 1 x FAKRA C plug            |
| Connector 2: | 1 x I-PEX Inc., MHF® I plug |

## Physical characteristics

|               |       |
|---------------|-------|
| Cable type:   | 1.13  |
| Cable length: | 20 cm |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

