

ESD Sweaters



45% Polyester; 45% cotton, 10% conductive fibers

Weight: 300 g/m2

Wrinkle-free treatment


Long sleeves with ESD elastic cuffs and round neck

ESD symbol on left arm

Unisex sizes: S -3XL (others on request)

Custom logos and staff names on request

Size	Black	Grey
S	STC40230302	STC40210102
M	STC40230303	STC40210103
L	STC40230304	STC40210104
XL	STC40230305	STC40210105
2XL	STC40230306	STC40210106
3XL	STC40230307	STC40210107



Resistivity point-point (Rp): 10⁶- 10⁷Ohms
Decay time: < 2 seconds
Conforms to current ESD Standards;
IEC61340-5-1 & ANSI/ESD S20.20

Size	A	B	C	D	E
S	47	49	49	59	64
M	48	52	52	60	65
L	50	54	54	61	67
XL	51	57	57	62	68
2XL	53	59	59	63	70
3XL	54	62	62	64	71

The electrical properties are retained,
even after 50 industrial washes.

- Wash at maximum 40°C
- Ironing at maimum 110°C
- Do not bleach
- Do not dry clean
- Do not tumble dry
- Do not use fabric softners

ESD Tec-Fabric Vests



75% Rayon/cotton; 15% polyester

6% spandex, 4% conductive fibers

Weight: 400 g/m2

Wrinkle-free treatment


Closure and 2-side pockets with zipper

ESD-sign at left front side

Unisex sizes: S -3XL (others on request)

Custom logos and staff names on request

Size	Navy Blue	Black
S	STC50225252	STC50230302
M	STC50225253	STC50230303
L	STC50225254	STC50230304
XL	STC50225255	STC50230305
2XL	STC50225256	STC50230306
3XL	STC50225257	STC50230307



Resistivity point-point (Rp): 10⁶- 10⁷Ohms
Decay time: < 2 seconds
Conforms to current ESD Standards;
IEC61340-5-1 & ANSI/ESD S20.20

Size	A	B	C	D	E
S	48	52	52	63	68
M	50	55	55	64	70
L	51	57	57	65	71
XL	53	59	59	66	73
2XL	54	63	63	67	74
3XL	56	67	67	68	76

The electrical properties are retained,
even after 50 industrial washes.

- Wash at maximum 40°C
- Ironing at maimum 110°C
- Do not bleach
- Do not dry clean
- Do not tumble dry
- Do not use fabric softners