




Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P



1 alphanumeric display 4-digit

2 status LEDs

3 programming button

4 G1 sealing cone external thread

Attention: The unit must only be installed in a process connection for G1 sealing cone.
The G1A sealing cone of the unit is only suited for adapters with metal end stop.

5 groove with sealing ring



ACS



CRN



US

LISTED

EC 1935/2004 EHEDG Tested FCM FDA



IO-Link

Reg31

UK CA

Product characteristics

Number of inputs and outputs

Number of digital outputs: 2; Number of analogue outputs: 1

Measuring range

-50...1000 mbar

-0.72...14.5 psi

-20...401.5 inH₂O

-5...100 kPa

Process connection

threaded connection G 1 external thread sealing cone Attention: The unit must only be installed in a process connection for G1 sealing cone.; The G1A sealing cone of the unit is only suited for adapters with metal end stop.

Application

Special feature

Gold-plated contacts

Application

flush mountable for the food and beverage industry

Media

viscous media and liquids with suspended particles; liquids and gases

Medium temperature

[°C]

-25...150

Min. bursting pressure

30000 mbar

435 psi

3000 kPa

Pressure rating

10000 mbar

145 psi

1000 kPa

Vacuum resistance

-1000 mbar

-0.1 MPa

Type of pressure

relative pressure; vacuum

No dead space

yes

MAWP (for applications according to CRN)

[bar]

10



Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

Electrical data					
Min. insulation resistance	[MΩ]	100; (500 V DC)			
Protection class		III			
Reverse polarity protection		yes			
Integrated watchdog		yes			
2-wire					
Operating voltage	[V]	20...30 DC			
Current consumption	[mA]	3.5...21.5			
Power-on delay time	[s]	< 1			
3-wire					
Operating voltage	[V]	18...30 DC			
Current consumption	[mA]	5...45; (430 bei max. Laststrom)			
Power-on delay time	[s]	< 0.5			
Inputs / outputs					
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1			
Outputs					
Total number of outputs		2			
Output signal		switching signal; analogue signal; IO-Link			
Electrical design		PNP/NPN			
Number of digital outputs		2			
Output function		normally open / normally closed; (parameterisable)			
Number of analogue outputs		1			
Analogue current output	[mA]	4...20, invertible; (scalable)			
Short-circuit protection		yes			
Type of short-circuit protection		pulsed			
Overload protection		yes			
2-wire					
Max. load	[Ω]	300			
3-wire					
Max. voltage drop switching output DC	[V]	2			
Permanent current rating of switching output DC	[mA]	100			
Switching frequency DC	[Hz]	125			
Max. load	[Ω]	(Ub - 10 V) / 21,5 mA; 650 Ω (Ub = 24 V)			
Measuring/setting range					
Measuring range		-50...1000 mbar	-0.72...14.5 psi	-20...401.5 inH2O	-5...100 kPa
Set point SP		-49...1000 mbar	-0.7...14.5 psi	-19.5...401.5 inH2O	-4.9...100 kPa
Reset point rP		-50...999 mbar	-0.73...14.48 psi	-20.1...400.9 inH2O	-5...99.9 kPa
Analogue start point		-50...800 mbar	-0.73...11.6 psi	-20.1...321.2 inH2O	-5...80 kPa
Analogue end point		150...1000 mbar	2.18...14.5 psi	60.2...401.5 inH2O	15...100 kPa
Min. difference between SP and rP		2 mbar	0.03 psi	0.6 inH2O	0.2 kPa
In steps of		1 mbar	0.01 psi	0.1 inH2O	0.1 kPa



Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

Factory setting		SP1 =250 mbar	rP1 = 230 mbar
		SP2 = 750 mbar	rP2 = 730 mbar
		ASP = 0.00 mbar	AEP = 1000 mbar
		dAP = 2.00 s	dAA =2.00 s
Temperature monitoring			
Measuring range		-25...150 °C	-13...302 °F
Accuracy / deviations			
Switch point accuracy [% of the span]		< ± 0,2; (DIN EN IEC 62828-1; Turn down 1:1)	
Repeatability [% of the span]		< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation [% of the span]		< ± 0,2; (DIN IEC EN 62828-1 incl. zero point and span error, non-linearity, hysteresis; Turn down 1:1)	
Linearity deviation [% of the span]		< ± 0,15; (Turn down 1:1)	
Hysteresis deviation [% of the span]		< ± 0,15; (Turn down 1:1)	
Long-term stability [% of the span]		< ± 0,1; (Turn down 1:1; per year)	
Total deviation over temperature range		Temperature range	total deviation
		-25...15 °C	Characteristics deviation ± 0,05 % of the span / 10 K
		15...80 °C	Characteristics deviation
		80...150 °C	Characteristics deviation ± 0,1 % of the span / 10 K
Notes on the accuracy / deviation		for further details see section Diagrams and graphs	
Temperature monitoring			
Accuracy	[K]	± 2,5+ (0,08 x (Umgebungstemperatur - Mediumtemperatur))	
Repeatability	[K]	± 0,2	
Resolution	[K]	0.2	
Response times			
Damping process value dAP	[s]	0...99.99	
Damping for the analogue output dAA	[s]	0...99.99	
2-wire			
Step response time analogue output	[ms]	30	
3-wire			
Min. response time of switching output (dAP)	[ms]	3	
Step response time analogue output	[ms]	7	
Temperature monitoring			
Dynamic response T05 / T09	[s]	< 35 / < 135; (DIN EN 60751 water ; > 0,9 m/s)	
Interfaces			
Communication interface	IO-Link		
Transmission type	COM2 (38,4 kBaud)		



Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Function class	Designation
	0x4000	Identification and Diagnosis
	0x800A	Measurement Data Channel (standard resolution)
SIO mode	yes	
Required master port type	A	
Min. process cycle time [ms]	5.6	
IO-Link resolution pressure [mbar]	0.05	
IO-Link resolution temperature [K]	0.2	
IO-Link process data (cyclical)	function	bit length
	pressure	32
	temperature	32
	device status	4
	binary switching information	2
IO-Link functions (acyclical)	application specific tag; internal temperature; operating hours counter; switching cycles counter; Pressure peak counter	
Supported DeviceIDs	Type of operation	DeviceID
	default	1153
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 67; IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61326-1	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]	214	
Note on approval	factory certificate available as download at www.factory-certificate.ifm	
UL approval	UL Approval no.	J049
	File number UL	E174189
Mechanical data		
Weight [g]	386.1	
Housing	cylindrical	
Dimensions [mm]	Ø 50 / L = 106	
Materials	stainless steel (316L/1.4404); FKM; PTFE; PBT; PEI; PFA	
Materials (wetted parts)	ceramics (99.9 % Al2O3); stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4; PTFE	
Min. pressure cycles	100 million	
Tightening torque [Nm]	20	
Process connection	threaded connection G 1 external thread sealing cone Attention: The unit must only be installed in a process connection for G1 sealing cone.; The G1A sealing cone of the unit is only suited for adapters with metal end stop.	

PI1807



Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

Displays / operating elements		
Display	Display unit	LED, green
	switching status	LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Display unit	mbar; psi; kPa; inH2O	

Remarks	
Pack quantity	1 pcs.

Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

Connection



- 1 connection for 2-wire operation
- 2 connection for 3-wire operation
- OUT1 switching output / IO-Link
- OUT2 switching output / analogue output
- 3 connection for IO-Link parameter setting (P = communication via IO-Link)
- colours to DIN EN 60947-5-2
- Core colours
- BK = black
- BN = brown
- BU = blue
- WH = white




Flush pressure sensor with display

PI-001BREA01-MFRKG/US/ /P

Diagrams and graphs

ambient temperature influence on the accuracy



X temperature
Y total deviation