

PDM-SET-9-62

Set of insertion tools for installing membrane glands and rubber bushings

Description and application

The PDM-SET-9-62 set comprises 8 types of insertion tools for seating round membrane glands and rubber bushings in mounting holes. The set covers hole diameters from 9 mm to 62 mm. The insertion tools enable the installation of round glands and bushings which can have various shapes and be made of different materials with different hardness.

They allow easy and quick seating of the component in the mounting hole without damaging it or the housing.



Key features

- greatly reduce installation time
- reduce strain on fingers and wrists
- assembly without damaging the element or the housing
- for glands of various material hardness

Set contents


Type	Hole diameters
PDM-9-11	9-11 mm
PDM-12-15	12-15 mm
PDM-16-23	16-23 mm
PDM-24-30	24-30 mm
PDM-31-37	31-37 mm
PDM-38-46	38-46 mm
PDM-47-54	47-54 mm
PDM-55-62	55-62 mm

Technical parameters

Parameter	Value
Set type	PDM-SET-9-62
Number of insertion tools in the set	8
Mounting hole diameter range	9-62 mm
Case material	polypropylene (PP)
Weight without packaging	495 g
Weight with packaging	730 g
Case dimensions	260 mm × 215 mm × 77 mm
Packaging dimensions	350 mm × 265 mm × 80 mm
GTIN number	5908130415112

Technical data is for information purposes only.

Operating instructions*



1. Place the installation tool into the mounting hole.
2. Pull the tool slightly to match the diameter of the spring elements to the diameter of the gland.
3. Place the gland in the correct position on the tool.
4. Pull the tool in the direction of the arrow until the gland is seated in the hole.
5. The moment of seating the gland.
6. Releasing and removing the tool.

* based on a sample version of the insertion tool

Publication date: 3 August 2026