


# PG2734



## Flush pressure sensor with analogue display

PG-010KREA01-MFRKG/US/ IP



- 1 analogue display
- 2 alphanumeric display 4-digit
- 3 sensor field (programming button)



| Product characteristics                        |                                                                       |              |
|------------------------------------------------|-----------------------------------------------------------------------|--------------|
| Number of inputs and outputs                   | Number of digital outputs: 1; Number of analogue outputs: 1           |              |
| Measuring range                                | -100...1000 kPa                                                       | -0.1...1 MPa |
| Process connection                             | threaded connection G 1 external thread Aseptoflex Vario              |              |
| Application                                    |                                                                       |              |
| Special feature                                | Gold-plated contacts                                                  |              |
| Application                                    | flush mountable for the food and beverage industry                    |              |
| Media                                          | viscous media and liquids with suspended particles; liquids and gases |              |
| Medium temperature [°C]                        | -25...125; (145 max. 1h)                                              |              |
| Min. bursting pressure                         | 15000 kPa                                                             | 15 MPa       |
| Pressure rating                                | 5000 kPa                                                              | 5 MPa        |
| Type of pressure                               | relative pressure; vacuum                                             |              |
| No dead space                                  | yes                                                                   |              |
| MAWP (for applications according to CRN) [bar] | 50                                                                    |              |



## Flush pressure sensor with analogue display

PG-010KREA01-MFRKG/US/ IP

| Electrical data                                 |                 |                                                                                                                    |
|-------------------------------------------------|-----------------|--------------------------------------------------------------------------------------------------------------------|
| Operating voltage                               | [V]             | 18...32 DC                                                                                                         |
| Current consumption                             | [mA]            | < 70; (24 V)                                                                                                       |
| Min. insulation resistance                      | [MΩ]            | 100; (500 V DC)                                                                                                    |
| Protection class                                |                 | III                                                                                                                |
| Reverse polarity protection                     |                 | yes                                                                                                                |
| Power-on delay time                             | [s]             | 6                                                                                                                  |
| Integrated watchdog                             |                 | yes                                                                                                                |
| Inputs / outputs                                |                 |                                                                                                                    |
| Number of inputs and outputs                    |                 | Number of digital outputs: 1; Number of analogue outputs: 1                                                        |
| Outputs                                         |                 |                                                                                                                    |
| Total number of outputs                         |                 | 2                                                                                                                  |
| Output signal                                   |                 | switching signal; analogue signal; (configurable)                                                                  |
| Electrical design                               |                 | PNP/NPN                                                                                                            |
| Number of digital outputs                       |                 | 1                                                                                                                  |
| Output function                                 |                 | normally open / normally closed; (parameterisable)                                                                 |
| Max. voltage drop switching output DC           | [V]             | 2                                                                                                                  |
| Permanent current rating of switching output DC | [mA]            | 250                                                                                                                |
| Switching frequency DC                          | [Hz]            | 50                                                                                                                 |
| Number of analogue outputs                      |                 | 1                                                                                                                  |
| Analogue current output                         | [mA]            | 4...20, invertible; (scalable)                                                                                     |
| Max. load                                       | [Ω]             | (U <sub>b</sub> - 10 V) / 20 mA                                                                                    |
| Short-circuit protection                        |                 | yes                                                                                                                |
| Type of short-circuit protection                |                 | pulsed                                                                                                             |
| Overload protection                             |                 | yes                                                                                                                |
| Measuring/setting range                         |                 |                                                                                                                    |
| Measuring range                                 |                 | -100...1000 kPa      -0.1...1 MPa                                                                                  |
| Set point SP                                    | [kPa]           | -98...1600                                                                                                         |
| Reset point rP                                  | [kPa]           | -100...1598                                                                                                        |
| Analogue start point                            | [kPa]           | -100...1350                                                                                                        |
| Analogue end point                              | [kPa]           | 150...1600                                                                                                         |
| In steps of                                     | [kPa]           | 1                                                                                                                  |
| Accuracy / deviations                           |                 |                                                                                                                    |
| Switch point accuracy                           |                 | < ± 0,2; (Turn down 1:1)                                                                                           |
|                                                 | [% of the span] |                                                                                                                    |
| Repeatability                                   |                 | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)                                                     |
|                                                 | [% of the span] |                                                                                                                    |
| Characteristics deviation                       |                 | < ± 0,2; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1) |
|                                                 | [% of the span] |                                                                                                                    |
| Linearity deviation                             |                 | < ± 0,15; (Turn down 1:1)                                                                                          |
|                                                 | [% of the span] |                                                                                                                    |
| Hysteresis deviation                            |                 | < ± 0,15; (Turn down 1:1)                                                                                          |
|                                                 | [% of the span] |                                                                                                                    |



## Flush pressure sensor with analogue display

PG-010KREA01-MFRKG/US/ IP

|                                                              |                                                                                                                           |                                                                                  |
|--------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Long-term stability<br>[% of the span]                       | < ± 0,1; (Turn down 1:1; per year)                                                                                        |                                                                                  |
| Temperature coefficient zero point<br>[% of the span / 10 K] | < ± 0,05; (0...70 °C)                                                                                                     |                                                                                  |
| Temperature coefficient span<br>[% of the span / 10 K]       | < ± 0,15; (0...70 °C)                                                                                                     |                                                                                  |
| Response times                                               |                                                                                                                           |                                                                                  |
| Response time [ms]                                           | < 10                                                                                                                      |                                                                                  |
| Damping process value dAP [s]                                | 0.01...30                                                                                                                 |                                                                                  |
| Damping for the analogue output dAA [s]                      | 0.01...30                                                                                                                 |                                                                                  |
| Step response time analogue output [ms]                      | 25                                                                                                                        |                                                                                  |
| Operating conditions                                         |                                                                                                                           |                                                                                  |
| Ambient temperature [°C]                                     | -25...80                                                                                                                  |                                                                                  |
| Storage temperature [°C]                                     | -40...100                                                                                                                 |                                                                                  |
| Protection                                                   | IP 67; IP 69K                                                                                                             |                                                                                  |
| Tests / approvals                                            |                                                                                                                           |                                                                                  |
| EMC                                                          | EN 61000-4-2 ESD                                                                                                          | 4 kV CD / 8 kV AD                                                                |
|                                                              | EN 61000-4-3 HF radiated                                                                                                  | 10 V/m                                                                           |
|                                                              | EN 61000-4-4 Burst                                                                                                        | 2 kV                                                                             |
|                                                              | EN 61000-4-5 Surge                                                                                                        | 0,5/1 kV                                                                         |
|                                                              | EN 61000-4-6 HF conducted                                                                                                 | 10 V                                                                             |
| Shock resistance                                             | DIN IEC 68-2-27                                                                                                           | 50 g (11 ms)                                                                     |
| Vibration resistance                                         | DIN IEC 68-2-6                                                                                                            | 20 g (10...2000 Hz)                                                              |
| MTTF [years]                                                 | 100                                                                                                                       |                                                                                  |
| Note on approval                                             | factory certificate available as download at <a href="http://www.factory-certificate.ifm">www.factory-certificate.ifm</a> |                                                                                  |
| Mechanical data                                              |                                                                                                                           |                                                                                  |
| Weight [g]                                                   | 524                                                                                                                       |                                                                                  |
| Dimensions [mm]                                              | 153 x 100 x 57                                                                                                            |                                                                                  |
| Materials                                                    | stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm                                  |                                                                                  |
| Materials (wetted parts)                                     | ceramics (99.9 % Al2O3); stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4; PTFE                    |                                                                                  |
| Min. pressure cycles                                         | 100 million                                                                                                               |                                                                                  |
| Process connection                                           | threaded connection G 1 external thread Aseptoflex Vario                                                                  |                                                                                  |
| Displays / operating elements                                |                                                                                                                           |                                                                                  |
| Display                                                      | Display unit                                                                                                              | 2 x LED, green                                                                   |
|                                                              | switching status                                                                                                          | LED, yellow                                                                      |
|                                                              | switch points                                                                                                             | LED ring, red                                                                    |
|                                                              | function display                                                                                                          | alphanumeric display, red 4-digit                                                |
|                                                              | measured values                                                                                                           | analogue display, 0...350° rotatable, pointer not visible when unit disconnected |
|                                                              | measured values                                                                                                           | alphanumeric display, red 4-digit                                                |
| Extended display range (max.)                                | 1600 kPa                                                                                                                  | 1.6 MPa                                                                          |

PG2734




Flush pressure sensor with analogue display

PG-010KREA01-MFRKG/US/    /P



| Remarks       |                                                                                                                                                      |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Remarks       | characteristics deviation in the extended display range: 1.5 % of the span<br>switch point accuracy in the extended display range: 1.5 % of the span |
| Pack quantity | 1 pcs.                                                                                                                                               |

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1                    switching output  
OUT2                    analogue output