

Adapter cable USB Type-A to Serial RS-232 RJ9/RJ10 with ESD protection Celestron NexStar 2 m

Opis

This USB to RS-232 RJ9 / RJ10 adapter cable by Delock is suitable for the PC operation of hand control boxes by the Celestron Telescopes. With the appropriate astronomy applications, the position of the telescope can be controlled by the computer or a firmware update can be carried out.



Numer artykułu 66734

EAN: 4043619667345

Kraj pochodzenia: China

Opakowanie: Torba na zamek błyskawiczny

Szczegóły techniczne

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x Serial RS-232 RJ9 / RJ10 plug
- Chipset: FTDI FT231X
- Plug & Play
- FIFO: 512 Byte - TX
- FIFO: 512 Byte - RX
- Compatible with USB 3.0, USB 2.0, and USB 1.1 full speed 12 Mbps
- Data transfer rate up to 230.4 Kb/s
- Signals: RXD(1), GND(2), TXD(4)
- ESD protection IEC 61000-4-2
 - HCP & VCP: ± 4 kV
 - Air Discharge: ± 8 kV
 - Contact Discharge: ± 4 kV
- Colour: black
- Cable length incl. connectors: ca. 2.0 m
- Suitable for various Celestron hand controllers


Wymagania systemowe

- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Zawartość opakowania

- Adapter cable USB 2.0 Type-A to RS-232 RJ9 / RJ10

Zdjęcia



Ogólne

Specyfikacja:	RS-232 (EIA / TIA) USB 2.0
Obsługiwany system operacyjny:	Windows 10 32-bit Windows 10 64-bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interfejs

Złącze 1:	1 x USB 2.0 Typ-A męski
Złącze 2:	1 x RJ9 Stecker

Właściwości techniczne

Chipset:	FTDI FT231XS
Szybkość transmisji danych:	230,4 Kbps
FIFO:	512 byte
Transmisja sygnału:	TxD, RxD und GND
UART:	USB to serial UART

Właściwości fizyczne

Długość kabla ze złączem:	2 m
Kolor:	czarny
Ochrona przed przepięciami:	±15 kV ESD Human Body Model (HBM)

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de