

Cable BNC male to BNC male 15 m

Description

This cable by Delock is used for connection of instruments of measurement technology as well as video transmission systems.

Tighter grip

Thanks to the bayonet lock, it can withstand stronger tensile stress and reduces susceptibility to interference, which is particularly relevant in event technology, for example.



Item no. 80086

EAN: 4043619800865

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x BNC male >
 - 1 x BNC male
- Impedance: 75 Ohm
- Cable type: coaxial
- Cable type: RG-59
- Cable attenuation: 0.25 dB @ 1 GHz per meter
- Cable diameter: ca. 6.1 mm
- Cable colour: black
- Length incl. connectors (L): ca. 15 m

System requirements

- Device with one free BNC port

Package content

- Cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x BNC male
Connector 2:	1 x BNC male

Technical characteristics

Impedance:	75 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable colour:	black
Cable length incl. connectors:	15 m
Conductor material:	copper

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

