

DATA SHEET

SUNGMUN CODE : NSI-10HS-TR

DESCRIPTION : SLIDE SWITCH

SUNGMUN ELECTRONICS CO., LTD.

Address 301-302,Bucheon Technopark 345, Seokcheon-ro, Ojeong-gu
Bucheon-si, Gyeonggi-do, Korea

TEL. +82-32-328-1941~4

FAX +82-32-328-1945








E-mail sungmun@sungmun.co.kr

Website www.sungmun.com

REV. NO.	DATE	REVISION	DR	CH	APP
△	22.12.06	CHANGE THE MARKING	H.S LEE	K.N KIM	W.J LEE
△	23.09.18	DIN ISO-2768-1m tolerance applied	H.S LEE	K.N KIM	W.J LEE

SPECIFICATION

1. Rating : DC12V 0.5A~24V 0.3A.
2. Contact Resistance : 30mΩ Max.
3. Travel : 1.6mm.
4. Operating Force : 250gf ± 150gf.
5. Life Cycle : 2,000 Cycle (with load).
6. Packing : 200pcs Vinyl Bag / 1,500pcs Reel Packing



△	BEFORE	AFTER
NSI10KOREA		SUNGMUN

DRAW/DESIGNED				CHECKED		APPROVED		G.TOL		TITLE	
J.S YANG				W.J LEE		K.I LEE		±0.1		MINI SLIDE SWITCH	
2021-11-15				2021-11-15		2021-11-15		mm		MODEL NO.	
SUNGMUN ELECTRONICS CO.,LTD				3:1		SIZE		A4		DRAW NO.	
										NSI-10HS-05	
										REV.	
										05	

1. Electrical Characteristics :

- 1.1 Rating : AC, DC 12V 0.5A~24V 0.3A (Minimum current: 1mA)
- 1.2 Contact Resistance : Max 30 mΩ
- 1.3 Insulation Resistance : Min 10,000 MΩ at DC 500V
- 1.4 Withstanding Voltage : 1min at AC 500V

2. Mechanical Characteristics :

- 2.1 Operating Force : 250gf ± 150gf
- 2.2 Travel : 1.6mm
- 2.3 Insulator :
 - 2.3.1 Case : Glass Fiber resin
 - 2.3.2 Slide : Glass Fiber resin
- 2.4 Terminal : Nickel, Gold Plate

3. Life Test :

- 3.1 Test Condition : Operations at a rate of 15-20 cycles in 1 minute
 - 3.1.1 With load : 2,000 cycles
 - 3.1.2 Without load : 10,000 cycles
- 3.2 Operating Force : With +40%, -40% of Initial Value
- 3.3 Contact Resistance : Max 200mΩ

4. Environmental Characteristics :


- 4.1 Operating Temperature : -40°C to +85°C
- 4.2 Storage Temperature : -40°C to +85°C
- 4.3 Humidity Test :
 - 4.3.1 Test Conditions : Measured 1hour after exposure to ambient
After 96hours exposure at 40±2°C, 90-95% R.H
 - 4.3.2 Insulation Resistance : Min 100MΩ, at DC 500V
 - 4.3.3 Withstanding Voltage : 1min at AC 250V

5. Solder Conditions :

5.1 Hand Solder : 3~4 sec. at 350°C (Dipping type)

5.2 Wave Solder : 5 sec. at 260°C (Dipping type)

5.3 Reflow Solder (SMD type)




5.3.1 Condition for Soldering

Profile Feature	Pb-Free Assembly
Average Ramp-UP Rate($T_s \text{ max}$ to T_P)	3°C/second max
Preheat - Temperature Min($T_s \text{ min}$) - Temperature Max($T_s \text{ max}$) - Time ($t_s \text{ min}$ to $t_s \text{ max}$)	150°C 200°C 60-180seconds
Time maintained above: - Temperature (T_L) - Time (t_L)	217°C 60-150seconds
Peak/Classification Temperature(T_P)	260°C +0°C/ -5°C
Time within 5°C of actual Peak Temperature(T_P)	5~10 seconds
Ramp-Down Rate	6°C/sec max
Time 25°C to Peak Temperature	8 minutes max

24M/M

REV. NO.	DATE	REVISION	DR	CH	APP
	23.10.13	Recreation of drawings for unification of drawing formats	H.S LEE	K.N KIM	W.J LEE



- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOL ± 0.2
 2. CAMBER NOT TO EXCEED 1mm IN 250mm.
 3. MATERIAL : BLACK CONDUCTIVE POLYSTYRENE.
 4. K₀ MEASURED FROM A PLANE ON THE INSIDE BOTTOM OF THE POCKET TO THE TOP SURFACE OF THE CARRIER.
 5. POCKET POSITION RELATIVE TO SPROCKET HOLE MEASURED AS TRUE POSITION OF POCKET, NOT POCKET HOLE.
 6. ALL DIMENSIONS ARE IN MILLIMETERS.

TOLERANCE
DECIMALS ANGULAR
X.X ± 0.13 $\pm 1^\circ$
X.XX ± 0.10

REEL	TYPE	COLOR	HUB	SIZE
	PLASTIC	BLACK	80	330
SHEET	BLACK 24MMX0.3	PACKING QUANTITY	1500/REEL	

DRAW/DESIGNED	CHECKED	APPROVED	G.TOL	TITLE
W.J LEE	J.P ROH	K.I LEE	--	MSI Series SMD Reel Packing
2018-11-16	2018-11-16	2018-11-16	UNIT mm	MODEL NO.
SUNGJUN ELECTRONICS CO.,LTD			SCALE N:S	MSI-XXHS-REEL
			SIZE A4	TR-MSI-00HS-02
			DRAW NO.	REV.
				02