




CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
ON	NONE	ON
2-3	OPEN	2-1

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 25VDC; 2A @250VAC
5. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
6. INSULATION RESISTANCE: 1,000M ohm min.
7. DIELECTRIC STRENGTH: 1000V RMS @sea level
8. OPERATING TEMP.: -30°C to 85°C
- ▲ 9. HARDWARE: T100011 LOCK WASHER-QTY 1 PER SWITCH
T100015 LOCK RING-QTY 1 PER SWITCH
T100000 HEX NUT-QTY 2 PER SWITCH
EACH COMPONENT TO BE PACKED SEPERATLY IN BAGS OF 1,000 PER BAG AND THEN ALL BAGS PACKED INTO LARGE BAG.
10. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®

B	13448	ADD SWITCH PART NUMBER	9/15/03	AR
A	13367	RELEASED FOR PRODUCTION	8/16/00	MM
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE 100SP1T2B3M1QE W/STD HARDWARE 1K PER BAG

SCALE 2:1	DATE 5/28/98	DR MM	DWG XT0115A	REV B
-----------	--------------	-------	-------------	-------