

Media Converter 10GBase-R SFP+ to SFP+

Description

This 10 Gigabit Ethernet Media converter by Delock can be used to connect different optical media. For example, Multi-mode fiber can be converted to Single-mode fiber. In the SFP slots, various optional 10 Gbps SFP+ modules by Delock can be used.



Item no. 86472

EAN: 4043619864720

Country of origin: China

Package: White Box

Technical details

- Connectors:
2 x SFP slot for 10GBase-R SFP+ module
(SFP module not included)
- Data transfer rate up to 10 Gbps
- IEEE 802.3ae compliant
- 6 LEDs for status monitoring
- Power consumption: max. 4 W
- Operating temperature: -20 °C ~ 60 °C
- Metal housing
- Fanless
- Dimensions (LxWxH): ca. 110 x 95 x 26 mm

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: KA1201A-1201000EU
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.4 A
- Output voltage / Output current / Output power: 12.0 V / 1.0 A / 12.0 W
- Average active efficiency: 83.7 %
- Efficiency at low load (10 %): 78.0 %
- No-load power consumption: 0.08 W

- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

System requirements

- 10GBase-R SFP+ module

Package content

- Media converter
- Power supply
- User manual

Images



Interface

Output:	1 x SFP jack
Input:	1 x SFP jack

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 10 Gbps
Operating temperature:	-20 °C ~ 60 °C

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	110 mm
Width:	95 mm
Height:	26 mm

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.4 A
Power supply output:	12.0 V / 1.1 A

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

