



Model: **AK-SC-E14**



Product code	AK-SC-E14
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Number of phases	1 phase
Maximum current	32 A
Power supply connector	Type 2 (IEC 62196-2) Female Connector
Plated plugs	Silver
Product color	White
Product size (L x W x H)	260 x 70 x 65 mm
Net weight	363 g
EAN code	5901720139498



Description

The Akyga® AK-SC-E14 Type 2 plug is the perfect solution for those facing the challenge of repairing or replacing a damaged EVSE cable, charger or adapter. It helps restore full functionality **to EV charging devices** whose Type 2 charging connector has failed. This connector is widely used in electric vehicles manufactured for the European market.

The Type 2 female connector is made from materials that are highly resistant to mechanical damage, such as drops or pressure, ensuring durability and reliability for years. **The silver-plated pins** used provide additional protection against corrosion and allow for **a current load of up to 32 A**.

A 220 Ω resistor, crucial for a correct charging process, is included. To ensure the safety and optimum performance of the system, installation of the plug should be carried out by a professional with the appropriate skills and knowledge. Incorrect mounting of the component can lead to serious consequences, including material damage or hazards to health and life, such as from electric shock.