
DATASHEET

SMD ▪ A
95-21SYGD/S530-XX/XXX



TR7 TR9 TR10 95-21

Features

- Package in 12mm tape on 7″ diameter reel.
- Compatible with automatic placement equipment.
- EIA Std. package.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm)

Description

- The 95-21 SMD LED is much smaller than leaded components .
  Thus enable smaller board size. Higher packing density. Reduced storage space and finally smaller equipment to be obtained.
- Besides, light weight makes them ideal for miniature applications.
- Furthermore by automation assembly machines the accuracy is anticipated.

Applications

- Small indicator for indoor applications.
- Flat backlight for LCD, switches and symbols.
- Indicator and backlight in office equipment.
- Indicator and backlight for battery driven equipment.
- Indicator and backlight for audio and video equipment.
- Backlighting in dashboards and switches.
- Telecommunication：indicator and backlighting in telephone and fax.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4

Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)

Device Selection Guide

Chip Materials	Emitted Color	Resin Color
AlGaInP	Green	Green Diffused

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_R	5	V
Forward Current	I_F	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	60	mA
Power Dissipation	Pd	60	mW
Operating Temperature	T_{opr}	-40 ~ +85	℃
Storage Temperature	Tstg	-40 ~ +90	℃
Electrostatic Discharge	ESD_{HBM}	2000	V
Soldering Temperature	T_{sol}	Reflow Soldering : 260 ℃ for 10 sec. Hand Soldering : 350 ℃ for 3 sec.	

Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Chip Rank	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	Iv	E1	50	80	-----	mcd	
		E2	75	100	-----		
		E3	100	125	-----		
		E4	125	160	-----		
Viewing Angle	$2\theta_{1/2}$	-----	-----	30	-----	deg	I_F=20mA
Peak Wavelength	λp	-----	-----	575	-----	nm	
Dominant Wavelength	λd	-----	-----	573	-----	nm	
Spectrum Radiation Bandwidth	△λ	-----	-----	20	-----	nm	
Forward Voltage	V_F	-----	1.7	2.0	2.4	V	
Reverse Current	I_R	-----	-----	-----	10	μA	V_R=5V


Note:
1.Reverse Voltage(VR) Condition is applied to IR test only The device is not designed for reverse operation

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4


Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)

Typical Electro-Optical Characteristics Curves


Spectrum Distribution




Forward Current vs. Forward Voltage




Luminous Intensity vs. Ambient Temperature




Luminous Intensity vs Forward Current



Forward Current Derating Curve




Radiation Diagram




Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)

Package Outline Dimensions




TR7




TR9

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)



TR10



直腳

Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.

Note: The tolerances unless mentioned are ±0.1, unit=mm.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)


Package Outline Dimensions

Label Explanation



- CPN: Customer's Product Number
- P/N: Product Number
- LOT No: Lot Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank


Reel & Carrier Tape Dimensions




Note: The tolerances unless mentioned are ±0.1, unit=mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)


Loaded quantity 1000 PCS per reel



TR7



TR9




TR10

Note: The tolerances unless mentioned are ±0.1, unit=mm.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)

Moisture Resistant Packaging



Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

2.1 Do not open moisture proof bag before the products are ready to use.

2.2 Before opening the package: The LEDs should be kept at 30℃ or less and 90%RH or less.

2.3 After opening the package: The LED's floor life is 72 hours under 30℃ or less and 60% RH or less.

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.


Baking treatment : 60±5℃ for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4

Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)



3.2 Reflow soldering should not be done more than two times.

3.3 When soldering, do not put stress on the LEDs during heating.


3.4 After soldering, do not warp the circuit board.

4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350℃ for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4
www.everlight.com
Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)

DISCLAIMER

1.EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2.The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3.The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4.When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5.These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6.This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : 29-Nov-2022. Issue No:DSE-0010521 Rev.4

Ver.:4 Release Date:12/09/2022 狀態:Approved(正式發行)