
ST - ICT Test Probe

mm [inch]



ST1000 CG05 N

Minimum centers:	2.54 [.100]
Full travel:	6.35 [.250]
Working travel:	4.30 [.169]
Current rating:	8 A
Probe resistance:	< 20mΩ
Operating temperature:	-40°C up to +120°C
Plunger material:	BeCu / Gold plated
Barrel material:	PhBr / Gold plated
Spring material:	Stainless Steel

Spring force at working stroke: 2.0 N [7.2 oz]

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!


	Name	Date
Designed	M.K.	2024.05.17
Drawed		
Checked		
Note		

Catalog Item: **ST1000 CG05 N**

Drawing No.:

A4 SHEET 1 OF 2

EQUIP TEST
TEST - SUPPORT - INNOVATE



Tools for the Test Probe

Tool Handle:	TH1
Universal Insertion Bit:	TBP10000
Insertion Bit:	TBP10070

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Insertion/Extraction:	TH2
Universal Insertion Bit:	TBP10000
Insertion Bit:	TBR10035
Extraction Bit:	TBR10070

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2024.05.17
Drawed		
Checked		
Note		

Catalog Item: **ST1000 CG05 N**

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST · SUPPORT · INNOVATE