

16V COMBI


DESCRIPTION

Combi antenna for roof mounting.

Designed to receive the **AM/FM** analogue radio and the **DAB** digital radio.



DIMENSIONS



TECHNICAL FEATURES	AM/FM	DAB
Frequencies	520 - 1710 kHz / 87,5 - 108 MHz	174 - 240 MHz
Power supply	+ 12 Volt Dedicated	
Consumption	75 mA (± 10 mA)	
Impedance	50 Ω	50 Ω
Gain	FM: 2,5 dBi (Peak)	13 dBi (Peak)
VSWR	AM: < 2,5:1 / FM: < 3,5:1	< 2,5:1
Polarization	Vertical	Vertical
Connector	FAKRA Male WHITE (code B)	FAKRA Male BLACK (code A)
Cable type	RG 174	RG 174
Cable length	200 mm	245 mm
Power supply connector	Faston Female with WHITE cover	
Power supply cable info	Unipolar / Black colour / 0,50 mm ²	
Power supply length	200 mm	
Extension cables	Not included	
Rod type	Antinoise	
Rod length	300 mm	
Rod thread	M5	
Mounting	Metal surface	
Coachwork drilling	Square: 15 x 15 mm / Round: Ø 19 mm	
Weight	100 g	
Tightening torque	6,5 Nm ± 20%	
Temperature	Working: -40° to +95° / Storage: -40° C to +105° C	
IP protection grade	IP68	

DISCLAIMER – Products, information, drawings, specifications and reference numbers (hereafter “contents”) discussed herein are for reference purposes only. All contents herein are provided on an “as is” basis, without warranties of any kind. The contents discussed herein remain the sole and exclusive property of MTA S.p.A. and shall not be copied, translated in whole or in part without MTA S.p.A. prior written consent. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted under this document, by implication, estoppel or otherwise. Contents may be modified and changed by MTA S.p.A. without any notice. For updates or additional information about MTA products, please contact your nearest MTA office. All brand names, trademarks and registered trademarks belong to their respective owners.