

Adapter cable USB 2.0 Type-A to Serial RS-232 with 9 open wires + Shielding 2 m

Opis

This USB 2.0 Type-A to serial RS-232 adapter cable by Delock is suitable as a connection cable between a device with USB 2.0 and a device with RS-232 port. Due to the tinned open cable ends, the connection can be made directly to the RS-232 device connector or flexible to various terminal blocks. In addition, it can be used to produce individual adapters and cable assemblies.



Numer artykułu 90416

EAN: 4043619904167

Kraj pochodzenia: China

Opakowanie: Torba na zamek błyskawiczny

Szczegóły techniczne

- Connectors:
1 x USB Type-A male
1 x Serial RS-232 9 x open wires + Shielding (tinned)
- Chipset: FTDI FT232R
- Compatible to UHCI / OHCI / EHCI controller
- Databits: 7 or 8
- Stop bits: 1 or 2
- Parity: none, space, even, odd, mark
- Data transfer rate up to 230.4 Kbps
- Pinout: TxD (red), RxD (braun), RTS (blau), CTS (purple), DTR (orange), DSR (grün), DCD (black), RI (white), GND (yellow), Shielding (matt black)
- ESD protection IEC 61000-4-2
HCP & VCP: ± 4 kV
Air Discharge: ± 8 kV
Contact Discharge: ± 4 kV
- Cable diameter: ca. 5 mm
- Cable gauge: 26 AWG
- Conductor: stranded copper wire
- Isolation: PVC
- Cable length incl. connectors: ca. 2 m
- Colour: black
- Operating temperature: -10 °C ~ 80 °C

Wymagania systemowe

- Mac OS 10.13 or above
- Linux Kernel 2.6 or above
- Windows 8.1/8.1-64/10/10-64/11
- Windows Server 2012 / Server 2012R2 / Server 2016
- PC or laptop with a free USB Type-A port

Zawartość opakowania

- USB Type-A to 1 x serial Adapter

Zdjęcia



Ogólne

Funkcja :	Plug & Play Converter
Specyfikacja:	RS-232 (EIA / TIA) USB 2.0
Obsługiwany system operacyjny:	Linux Kernel 2.6 lub nowszy Mac OS 10.9 lub nowszy Windows 10 32-bit Windows 10 64-bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Server 2012 R2 Windows Server 2012 Windows Server 2016

Interfejs

Złącze 1:	1 x USB 2.0 Typ-A męski
Złącze 2:	10 x otwarty cynowany

Właściwości techniczne

Chipset:	FTDI 232R
Szybkość transmisji danych:	230,4 Kbps
FIFO:	128 byte 256 Byte
Temperatura robocza:	-10 °C ~ 80 °C
Transmisja sygnału:	TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND + Shield
Transmisja danych:	asynchronous full duplex Half duplex Dwukierunkowa
UART:	USB to serial UART

Właściwości fizyczne

Kolor przewodu:	czarny
Długość kabla:	2 m
Wykończenie pinów:	pozlacane Tin-plated
Średnica kabla:	26 AWG 5 mm
Ochrona przed przepięciami:	±8 kV EN / IEC 61000-4-2 Wyładowanie przy kontakcie ±4 kV EN / IEC 61000-4-2 Contact Discharge ±4 kV EN / IEC 61000-4-2 VCP & HCP
Izolator:	PVC

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de