




Capacitive sensor

KI-3150QBPKG/SL/1P/IO



- 1 LED yellow switching status
- 2 potentiometer Sensing range



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range [mm]		0.5...40
Communication interface		IO-Link
Housing		threaded type
Dimensions [mm]		M30 x 1.5 / L = 92
Application		
Medium temperature [°C]		-25...110
Electrical data		
Operating voltage [V]		10...30 DC
Current consumption [mA]		< 22
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC [V]		2.5
Permanent current rating of switching output DC [mA]		200
Switching frequency DC [Hz]		30
Short-circuit protection		yes
Overload protection		yes
Detection zone		
Sensing range [mm]		0.5...40
Sensing range adjustable		yes
Factory setting sensing range [mm]		15
Real sensing range Sr [mm]		15 ± 10 %
Accuracy / deviations		
Hysteresis [% of Sr]		1...15



Capacitive sensor

KI-3150QBPKG/SL/1P/IO

Switch point drift	[% of Sr]	-15...15	
Interfaces			
Communication interface	IO-Link		
Transmission type	COM2 (38,4 kBaud)		
IO-Link revision	1.1		
SDCI standard	IEC 61131-9		
Profiles	Smart Sensor: Process Data Variable; Device Identification		
SIO mode	yes		
Required master port type	A		
Min. process cycle time	[ms]	20	
IO-Link functions (acyclical)	application specific tag; operating hours counter; normally open / normally closed (configurable); PNP / NPN (parametrierbar); switch point setting; Hysteresis		
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection	IP 65; IP 67; IP 69K		
Tests / approvals			
EMC	EN 61000-4-2	30 kV AD / 4 kV CD	
	EN 61000-4-3	10 V/m	
	EN 61000-4-4	2 kV	
	EN 61000-4-6	10 V	
	EN 55011	class B	
Vibration resistance	DIN EN 60947-5-2	1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz	
Shock resistance	DIN EN 60947-5-2	30 g 6 shocks / 11 ms half-sine (x, y, z)	
MTTF	[years]	903.84	
UL approval	Ta	-25...60 °C	
	Enclosure type	Type 1	
	power supply	Limited Voltage/Current	
	UL Approval no.	D002	
	File number UL	E174191	
Mechanical data			
Weight	[g]	99.2	
Housing	threaded type		
Mounting	quasi flush		
Dimensions	[mm]	M30 x 1.5 / L = 92	
Thread designation	M30 x 1.5		
Materials	PBT; PC; POM		
Displays / operating elements			
Display	switching status	1 x LED, yellow	
Accessories			
Items supplied	lock nuts: 2		
Remarks			
Pack quantity	1 pcs.		

KI5305




Capacitive sensor

KI-3150QBPKG/SL/1P/IO

Electrical connection

Cable: 2 m, PUR, Ø 4 mm; 3 x 0.34 mm²

Connection



BK: OUT / IO-Link
Core colours :
BN = brown
BU = blue
BK = black