

1128BAX

Double-acting electricians' scissors, with milling profile in DLC-coated stainless steel

Features:

- Double-acting cutting: a special cam on the fulcrum allows the blades to run lengthwise, which results in increased cutting power while closing the blades
- Milling profile: designed to enlarge holes on plastic, from 13 mm to 25 mm
- DLC coating: DLC (diamond-like carbon) is an innovative carbon-based coating: the high hardness and low coefficient of friction arise from the simultaneous presence of carbon on the surface in the form of graphite, and diamond
- High blade surface hardness (resistance to abrasion and wear)
- Low coefficient of friction (smoothness and anti-adherence)
- Anti-loose eccentric pin
- Large handles with pipe throttling grooves
- With articulated plastic case

Improved and longer lasting performance.

	art.	L mm	L1 mm	 mm ²
011280088	1128BAX	150	50	50





Technical sheet

No.

78NA01A

Issue

V01.0

Product family:

Electrical tapes - PVC electrical tape

Item code:

ESB1510BI, ESB1510BL, ESB1510GI, ESB1510GR, ESB1510GV, ESB1510MA, ESB1510NE, ESB1510RO, ESB1510VE, ESB1525BI, ESB1525BL, ESB1525GI, ESB1525GR, ESB1525GV, ESB1525MA, ESB1525NE, ESB1525RO, ESB1525VE, ESB1925BI, ESB1925BL, ESB1925GI, ESB1925GR, ESB1925GV, ESB1925MA, ESB1925NE, ESB1925RO, ESB1925VE, ESB2525BI, ESB2525BL, ESB2525GI, ESB2525GR, ESB2525GV, ESB2525MA, ESB2525NE, ESB2525RO, ESB2525VE

Description:

ELECTRICAL TAPE · PVC · 0.15 THICKNESS

Image



Specifications

MATERIAL:

PVC

RESISTANT TO:

acids, weathering, corrosion, alkalis, oil, humidity

OPERATING TEMPERATURE:

0°C - +90°C

TENSILE STRENGTH:

28 N/cm equivalent to 18.6 N/mm²

ELONGATION:

200

ADHESION TO STEEL:

2.2

ADHESION TO BACKING:

2

DIELECTRIC STRENGTH:

45

DIELECTRIC STRENGTH:

45 kV/mm

ACCORDING TO STD.:

IEC 60454-2

FLAMMABILITY:

flame retardant

CLASSIFICATION:

EN 60454-3-1-5/F-PVCP/90

ACCORDING TO STD.:

IEC 60454-2

Code	Color	Thickness (mm)	Height (mm)	Length (m)	
ESB1510BI	 White	0,15	15	10	10/200
ESB1510BL	 Blue	0,15	15	10	
ESB1510GI	 Yellow	0,15	15	10	
ESB1510GR	 Grey	0,15	15	10	
ESB1510GV	 YellowGreen	0,15	15	10	
ESB1510MA	 Brown	0,15	15	10	
ESB1510NE	 Black	0,15	15	10	
ESB1510RO	 Red	0,15	15	10	
ESB1510VE	 Green	0,15	15	10	
ESB1525BI	 White	0,15	15	25	10/100
ESB1525BL	 Blue	0,15	15	25	
ESB1525GI	 Yellow	0,15	15	25	
ESB1525GR	 Grey	0,15	15	25	
ESB1525GV	 YellowGreen	0,15	15	25	
ESB1525MA	 Brown	0,15	15	25	
ESB1525NE	 Black	0,15	15	25	
ESB1525RO	 Red	0,15	15	25	
ESB1525VE	 Green	0,15	15	25	
ESB1925BI	 White	0,15	19	25	10/100
ESB1925BL	 Blue	0,15	19	25	
ESB1925GI	 Yellow	0,15	19	25	
ESB1925GR	 Grey	0,15	19	25	
ESB1925GV	 YellowGreen	0,15	19	25	
ESB1925MA	 Brown	0,15	19	25	
ESB1925NE	 Black	0,15	19	25	
ESB1925RO	 Red	0,15	19	25	
ESB1925VE	 Green	0,15	19	25	
ESB2525BI	 White	0,15	25	25	8/80
ESB2525BL	 Blue	0,15	25	25	
ESB2525GI	 Yellow	0,15	25	25	
ESB2525GR	 Grey	0,15	25	25	
ESB2525GV	 YellowGreen	0,15	25	25	
ESB2525MA	 Brown	0,15	25	25	
ESB2525NE	 Black	0,15	25	25	
ESB2525RO	 Red	0,15	25	25	
ESB2525VE	 Green	0,15	25	25	



FLAME

RETARDANT

BM SPA - Viale Milano 54/56 - 20089 Rozzano (MI) Italy