

Antenna Cable SMA jack bulkhead ferrite core to I-PEX Inc., MHF[®] I plug 1.13 20 cm thread length 10 mm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 89833

EAN: 4043619898336

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA jack bulkhead >
 - 1 x I-PEX Inc., MHF[®] I plug
- 1 x ferrite core
- Thread length: 10 mm
- Impedance: 50 Ohm
- Cable type: 1.13
- Cable: coaxial
- Cable attenuation: 3.2 dB @ 2.4 GHz per meter
- Cable diameter: ca. 1.13 mm
- Colour: grey
- Length incl. connectors (L): ca. 20 cm

System requirements

- Device with one free SMA or I-PEX Inc., MHF[®] I port

Package content

- Antenna cable
- Locking ring, nut, toothed washer

Interface

Connector 1:	1 x SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Ferrite core:	1 x
Thread length:	10 mm
Cable category:	coaxial
Cable type:	1.13
Cable attenuation:	3.2 dB @ 2.4 GHz per meter
Cable colour:	grey
Cable length incl. connectors:	20 cm
Cable diameter:	1.13 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

