


KN12C606
CAPACITIVE SENSORS • INCREASED AMBIENT TEMPERATURE

sensor capacitive, M12x1 50long, Non-flush, Sn: 0.5-10, 10-35V DC, 100°C, PNP Programmable/configurable, Cable 2m Silicone, IP67, PTFE, Manual adjustment


MECHANICAL FEATURES

Active area material of sensor	Polytetrafluorethylene (PTFE)
Ambient temperature	-25 °C ... 100 °C
Cable length	2 m
Degree of protection (IP)	IP67
Design	Cylinder, screw-thread
Housing material	Polytetrafluorethylene (PTFE)
Increased ambient temperatures > 80°C	+
Material of cable sheath	Silicone
Mechanical mounting condition for sensor	Non-flush
Number of cores	4
Pressure-proof	-
Sensor length	50 mm
Teflon housing	+
Thread pitch	1 mm
Thread size, metric	12
Wire cross section	0.14 mm ²

ELECTRICAL FEATURES

Cascadable	-
Rated switching current	250 mA
Reverse polarity protection	+
Setting procedure	Manual adjustment
Short-circuit protection	+
Suitable for safety functions	-
Supply voltage	10 V ... 35 V
Switching distance	4 mm
Switching distance	0.5 mm ... 10 mm
Type of electrical connection	Cable
Type of switching function	Programmable/configurable
Type of switching output	PNP
Voltage type	DC
With monitoring function of downstream devices	-

OTHER FEATURES

Level detection	+
-----------------	---


Other

Packaging dimensions	77.0mm x 25.0mm x 123.0mm
Shipping weight	0.1kg
Tariff code	85365019

Classification

ipf product group	700
eClass 8.0	27270102
eClass 9.0	27270102
eClass 9.1	27270102
ETIM-5.0	EC002715
ETIM-6.0	EC002715
ETIM-7.0	EC002715

Connection



Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.