

Antenna Cable N plug > SMA plug CFD200/RF200 7.5 m low loss

Description

This high-quality coaxial cable ensures a reliable connection of components of the radio frequency technology. It is characterised by a very low attenuation.



Item no. 89419

EAN: 4043619894192

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x N plug >
 - 1 x SMA plug
- Impedance: 50 Ohm
- Cable type: CFD200, RF200
- Cable: coaxial
- Cable attenuation:
 - 0.55 dB @ 2.4 GHz per meter
 - 0.86 dB @ 5.7 GHz per meter
- Cable diameter: ca. 4.8 mm
- Cable colour: black
- Smallest bending radius: 12.7 mm
- Length incl. connectors (L): ca. 7.5 m

System requirements

- Device with one free N or SMA port

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x N male
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	CFD200 RF200
Cable attenuation:	0.55 dB @ 2.4 GHz per meter 0.86 dB @ 5.7 GHz per meter
Cable colour:	black
Cable length incl. connectors:	7.5 m
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

