


Fibre optic diffuse reflection sensor

FT-11-EPA-M6/F2X1/2M



Application

Function principle	Diffuse reflection sensor
Application	For use in industrial environments

Detection zone

Range with fibre optic amplifier type	OB50; OBF; OCF; OO50
---------------------------------------	----------------------

OB50

Range fibre optics	[mm]	70
--------------------	------	----

OBF

Range fibre optics	[mm]	100
--------------------	------	-----

OCF (High Power)

Range fibre optics	[mm]	630
--------------------	------	-----

OO50

Range fibre optics	[mm]	300
--------------------	------	-----

Operating conditions

Ambient temperature	[°C]	-40...70
---------------------	------	----------

Mechanical data

Weight	[g]	48.5
Version of sensing head		straight
Sensing head thread		M6

E20633



Fibre optic diffuse reflection sensor

FT-11-EPA-M6/F2X1/2M

Sensing head length	[mm]	35
Total length	[mm]	2000
Min. bending radius	[mm]	30
Fibre arrangement		⊙
Core diameter	[mm]	2 x 1
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE

Accessories

Items supplied	hexagon nuts: 2 x M6 (3,1 mm), stainless steel tooth lock washers: 2
Accessories (optional)	Cutter for fibre optics:, E20600

Remarks

Pack quantity	1 pcs.
---------------	--------