

Adapter USB 2.0 Type-A to 1 x Serial RS-232 D-Sub 9 pin male with screws 1.5 m

Description

This adapter by Delock enables the connection of a serial device via a USB Type-A port.



Item no. 62646

EAN: 4043619626465

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x serial DB9 male with screws
- Chipset: Prolific PL-2303 GS
- Data transfer rate up to 460.8 Kbps
- Signals: TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
- Parity: even, odd, none, mark, space
- Stop bits: 1, 1.5, 2
- Databits: 5, 6, 7, 8
- Flow control: none, Xon / Xoff, RTS / CTS
- Cable length incl. connectors: ca. 1.5 m

System requirements

- Linux Kernel 5.11 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB 2.0 to 1 x serial adapter
- Driver CD
- User manual

Images



General

Function:	Plug & Play
Specification:	RS-232 (EIA / TIA) USB 2.0

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x Serial RS-232 DB9 male

Technical characteristics

Chipset:	Prolific PL2303GS
Data transfer rate:	460.8 Kbps
FIFO:	1 x 1024 Byte
Signal transmission:	TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
Data transmission:	asynchronous full duplex
UART:	USB to serial UART
Data bits:	5, 6, 7, 8

Physical characteristics

Cable length incl. connectors:	1.5 m
Pin finishing:	gold-plated
Screw type:	#4-40 UNC
Shielding:	double shielded
Colour:	transparent black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de