



ST - ICT Test Probe

mm [inch]




ST1000 CG06 M

Minimum centers:	2.54 [.100]
Full travel:	6.35 [.250]
Working travel:	4.30 [.169]
Current rating:	8 A
Probe resistance:	< 20mΩ
Operating temperature:	-40°C up to +120°C
Plunger material:	BeCu / Gold plated
Barrel material:	PhBr / Gold plated
Spring material:	Stainless Steel

Spring force at working stroke: 1.5 N [5.4 oz]

 COPYRIGHT 2024 <i>EQUIP-TEST KFT.</i> <i>ALL RIGHTS RESERVED</i>		Name	Date	Catalog Item:		
	Designed	M.K.	2024.05.17	ST1000 CG06 M		
	Drawed					
	Checked					
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Note				Drawing No.:	
					A4	SHEET 1 OF 2
						

ST - ICT Test Probe



Tools for the Test Probe

Tool Handle: TH1
Universal Insertion Bit: TBP10000
Insertion Bit: TBP10070

Tools for the Receptacle

Tool Handle Insertion: TH1
Tool Handle Insertion/Extraction: TH2
Universal Insertion Bit: TBP10000
Insertion Bit: TBR10035
Extraction Bit: TBR10070

© COPYRIGHT 2024 EQUIP-TEST KFT. ALL RIGHTS RESERVED This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!		Name	Date	Catalog Item: ST1000 CG06 M		
	Designed	M.K.	2024.05.17	Drawing No.:		
	Drawed					
	Checked					
	Note				A4	SHEET 2 OF 2

EQUIPTEST

TEST - SUPPORT - INNOVATE