


SW = Switch Probe

mm [inch]



SW1202 FA03 L

Minimum centers: 3.05 (.120)
 Full travel: 7.50 (.295)
 Working travel: 5.00 (.197)
 Switching path: 0.65 (.026) ± 0.1 (.004)
 Current rating: 5 A (continuous)
 Probe resistance: < 50 mΩ
 Plunger material: BeCu - Gold Plated
 Barrel material: Brass - Gold Plated
 Spring material: MW - Gold Plated


Operating temperature: -40 °C up to +80 °C
(-40 °F up to +176 °F)

Spring force at working stroke: 1.50 N (5.4 oz)

© COPYRIGHT 2019 EQUIP-TEST KFT. ALL RIGHTS RESERVED		Name	Date	Catalog Item: SW1202 FA03 L		
	Designed	PGY	2024. 07. 03.			
	Drawed					
	Checked					
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Note	Drawing No.:			 TEST • SUPPORT • INNOVATE	
			A4	SHEET 2 OF 1		

SW = Switch Probe

mm [inch]



Tools for the Test Probe

Tool Handle:
Insertion bit:

TH1
TBP10000

© COPYRIGHT 2019 EQUIP-TEST KFT. ALL RIGHTS RESERVED		Name	Date	Catalog Item: SW1202 FA03 L		
	Designed	PGY	2024. 07. 03.			
	Drawed					
	Checked					
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Note	Drawing No.:			 TEST • SUPPORT • INNOVATE	
			A4	SHEET 2 OF 2		