






Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

3	1	MATING SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL
2	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
1	1	REAR SIDE	COPPER ALLOY	TIN PLATED
pos	qty	description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			tolerance	scale: 5 : 1
			dim. in mm	material: see partlist
			drawn 02.08.2010 Henneboel	title: HIGH POWER CONTACT MALE PREMATING SOLDER PIN 90°, d=3,2mm, 30A D-SUB COMBINATION
			appd. 02.08.2010 Fischer	
			norm	
DO NOT ALTER CAD DRAWING BY HAND			d-old	dwg no: Inventor 10
			a Origin	DIN-A3
rev.	description	date	name	sh: 1
part no: 131C13129X				

CONEC