

RS-232 Cable Serial D-Sub9 female to female null modem with narrow plug housing 10 m

Description

This serial cable by Delock is a **full handshaking null modem cable** for printers, measuring instruments, converters, RS-232 hubs, patch panels etc. With this cable, two serial RS-232 devices can be connected to each other for data exchange.

Mini D-Sub9 connector

These cables fit any RS-232 port, as the **mini D-Sub9 connectors** (44 x 33.3 x 15 mm) are small and compact. In this way, RS-232 connections can be used directly adjacent to each other.



10 m

Item no. 86604

EAN: 4043619866045

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x serial D-Sub9 female with screws >
 - 1 x serial D-Sub9 female with screws
- Cable gauge: 28 AWG
- Full handshaking cable
- Pin assignment: 1+6 - 4, 2 - 3, 3 - 2, 4 - 1+6, 5 - 5, 7 - 8, 8 - 7, shielded
- Colour: black
- Insulator: PVC
- Screw type: #4-40 UNC
- Cable diameter: ca. 5 mm
- Cable length incl. connectors: ca. 10 m

System requirements

- A free D-Sub9 male port


Package content

- Cable

Images



mini Sub-D 9



General

Specification:	RS-232 (EIA / TIA)
Style:	Null Modem Mini Sub-D9 both sides identical

Interface

Connector 1:	1 x serial D-Sub 9 female with screws
Connector 2:	1 x serial Sub-D 9 female with screws

Technical characteristics

Data transfer rate:	921.6 Kbps
Signal transmission:	TxD, RxD, RTS, CTS, DTR, DSR, DCD, GND

Physical characteristics

Cable type:	AWM Style 2464 28 AWG 80 °C 300 V VW-1
Cable length incl. connectors:	10 m
Pin finishing:	gold-plated
Conductor material:	Copper tinned
Cable gauge:	28 AWG
Screw type:	#4-40 UNC
Colour:	black
Cable diameter:	5 mm
Cable jacket material:	PVC
Safety of Flammability:	VW-1

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de