Product Data Sheet
GW40293TB
40 CDI Range




The widest range of flush-mounting switchboards and distribution boards available on the market today. Seven families designed to offer solutions in the residential and advanced tertiary sectors, also available in Halogen Free material. Versions from 2 to 72 modules, degrees of protection from IP40 to IP55 and specific versions also for plasterboard. Furthermore, the offer includes Multimedia Enclosures in compact (36 modules) and complete (54 modules) versions, both compliant with what is suggested by the CEI 306-2 guide.


Insulation class	II (according to IEC 61140 standards)	Colour	White
Outer dim. LxHxD (mm)	328x338x108	IP degree	IP40
Installation	Flush mounting enclosures	Dispersible power (W)	25
Mechanical resistance	IK08	Rated voltage	400V
Door colour	Blank	No. of modules EN 50022	24 (12X2)
Rated current	125 A	Glow Wire Test	650 °C
For walls	Brickwall	Operating temperature	-15 ÷ +60°C
Type of material	Halogen-free in compliance with EN 60754-2	Thermo-pressure with ball	70 °C
Standard	EN 60670-1 (CEI 23-48) IEC60670-24 CEI 23-49	Insulation voltage	750 V
Max. installable terminal blocks	2 x 12 modules		

BEHAVIOUR WITH CHEMICAL AND ATMOSPHERIC AGENTS

Saline solution	Acids		Bases		Solvents				Mineral oil	UV rays
	Concentrated	Diluited	Concentrated	Diluited	Hexane	Benzol	Acetone	Alcohol		
Resistant	Not resistant	Limited resistance	Not resistant	Limited resistance	Limited resistance	Not resistant	Not resistant	Limited resistance	Limited resistance	Limited resistance

DIMENSIONAL





TECHNICAL SYMBOLOGY

EN 61140
II (according to IEC 61140 standards)

IP
IP40

IK
IK08

GWT
650 °C

INSTALLATION
min -15°c
max +60°c
-15 ÷ +60°C

HF
HALOGEN FREE
Halogen-free in compliance with EN 60754-2

70 °C

STANDARDS/APPROVALS

CE Reach Declaration

GEWISS S.p.A. Via A. Volta, 1
24069 Cenate Sotto - Bergamo - Italy
tel. +39 035 94 61 11 fax +39 035 94 69 09
Company subject to the management and coordination of Polifin S.p.A.

www.gewiss.com
sat@gewiss.com
Last update 23/01/2026

Data, measures, designs and pictures are shown only as informative purposes, and could be changed without previous notice