

SPT=Threaded Step Probe

mm [inch]





SPT1001 RL40 M

Minimum centers:	2.54 (.100)
Full travel:	5.00 (.197)
Working travel:	4.00 (.157)
Current rating:	5 - 8 A
Probe resistance:	< 25 mΩ
Plunger material:	BeCu - Gold Plated
Barrel material:	Brass - Gold Plated
Spring material:	MW - Plated

Operating temperature: -40 °C up to +80 °C
(-40 °F up to +176 °F)

Spring force at working stroke: 1. 0N (3.6 oz)

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	BB	2025. 04. 22.
Drawed		
Checked		

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note

Catalog Item:
SPT1001 RL40 M

Drawing No.:


A4

SHEET 2 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE

SPT=Threaded Step Probe

mm [inch]



Tools for the Test Probe

Tool Handle:	TH3
Adjustable Torque Handle:	TTS01
Insertion/Extraction Bit:	TBT10077
Insertion/Extraction Bit:	TBT10078
Insertion/Extraction Bit:	TBT10079

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Insertion/Extraction:	TH2
Insertion Bit:	TBR10036
Extraction Bit:	TBR10071

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	BB	2025. 04. 22.
Drawed		
Checked		

Note

Catalog Item:
SPT1001 RL40 M

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE