



BETA 1233MQF/D4-FX

Set of four slim screwdrivers with electrician's scissors 1128FX



Features

The new set has been designed and conceived to provide you with the best tools, guaranteeing excellent performance in every situation.

PERFECT GRIP AND ANTI-ROLL

The embossed texture of the new handle, combined with the TPU material for greater adhesion, ensures a secure grip even in the most difficult conditions, while the enlarged handle optimises ergonomics, ensuring a stable and comfortable grip during the most precise operations.

PERFECT GRIP AND ANTI-ROLL

The embossed texture, combined with the TPU material for increased adhesion, ensures a secure grip even in the most difficult conditions, while the enlarged handle optimises ergonomics, ensuring a stable and comfortable grip during the most precise operations.

LARGE SECTION CABLE CUTTER THROAT

The integrated groove in the 1128FX electrician's scissor allows cables with cross-sections up to 50 mm² to be cut with ease and safety.



SLIM TECHNOLOGY

Slim technology reduces the blade diameter without altering the thickness of the insulator, improving convenience without compromising safety.



SLIM HANDLE

The slim handle ensures a secure and comfortable grip, offering greater manoeuvrability even in tight spaces.



FLAT CAP AND RECOGNITION

The flat handle at the end offers more thrust and facilitates identification due to the size imprint.

1128FX: n. 1
1234MQF/LP: n. 2 Screwdrivers for headless slotted screws 0,8X4-1,0X5,5 mm
1232MQF: n. 2 Screwdrivers for cross head Phillips® screws PH1-PH2

Coded items

	Art.
012330905	1233MQF/D4-FX





Scheda tecnica

No.

11FA01B

Versione

V01.1

Famiglia prodotto:

Fascette - Fascette in nylon UV resistant

Codici articolo:

N0824, N0824M, N1025, N1025M, N1225, N1625, N1625M, N2025, N1436, N1436M, N2036, N2936, N2936M, N3736, N1248, N1648, N1948, N2048, N2048M, N2548, N3048, N3048M, N3748, N3948, N4348, N5348, N1576, N2076, N2976, N3776, N4576, N5476, N7576, N4390, N5390, N7190, N7890, N8190, N1090, N1290, N1590

Descrizione:

FASCETTE IN NYLON RESISTENTI AI RAGGI UV - STANDARD

Immagine



Specifiche

MATERIALE:

poliammide (PA 6.6) + carbon black

COLORE:

nero

LIVELLO AUTOESTINGUENZA:

UL 94 V2

TEMPERATURA ESERCIZIO:

da -40 °C a +85 °C

TEMPERATURA MIN. INSTALLAZIONE:

-10 °C

RESISTENZA AGLI AGENTI CHIMICI:

buona resistenza alle basi, agli olii, ai grassi, ai solventi di cloruro. Limitata resistenza agli acidi. Non resistente ai fenoli.

NORME DI RIF.:

EN 62275:2015-02

CLASSIFICAZIONE:

tipo 1 (EN), tipo 21 (UL)

MONTAGGIO:

aprire la confezione poco prima dell'utilizzo

Codice	Larghezza (mm)	Lunghezza (mm)	Ø max di serraggio (mm)	Ø min di serraggio (mm)	Resistenza minima di trazione (N)	
N0824	2,5	80	14	3	80	100/8000
N0824M	2,5	80	14	3	80	1000/8000
N1025	2,5	100	20,5	3	80	100/5000
N1025M	2,5	100	20,5	3	80	1000/5000
N1225	2,5	120	27	3	80	100/5000
N1625	2,5	160	40	3	80	100/4000
N1625M	2,5	160	40	3	80	1000/4000
N2025	2,5	200	52,5	3	80	100/3000
N1436	3,6	140	33	3	180	100/2500
N1436M	3,6	140	33	3	180	1000/2500
N2036	3,6	200	52,5	3	180	100/2000
N2936	3,6	300	106	3	180	100/1500
N2936M	3,6	300	106	3	180	1000/1500
N3736	3,6	370	105	3	180	100/4000
N1248	4,6	120	24	3	220	100/2000
N1648	4,6	160	36	3	220	
N1948	4,8	188	46	3	220	100/1500
N2048	4,8	200	50	3	220	
N2048M	4,8	200	50	3	220	1000/1500
N2548	4,8	250	65	3	220	100/1300
N3048	4,8	300	81	3	220	100/1000
N3048M	4,8	300	81	3	220	1000/1000
N3748	4,8	370	103,5	3	220	100/3000
N3948	4,8	390	110	3	220	100/2500
N4348	4,8	430	122,5	3	220	100/1500
N5348	4,8	530	160	3	220	100/100
N1576	7,6	150	24	6	550	100/1000
N2076	7,6	200	51	6	550	100/800
N2976	7,6	300	83	6	550	100/600
N3776	7,6	370	103,5	6	550	100/1000
N4576	7,6	450	130,5	6	550	
N5476	7,6	540	159	6	550	100/100
N7576	7,6	750	226	6	550	
N4390	9	430	130,5	9	800	
N5390	8,8	550	163,5	9	800	
N7190	8,8	710	195	9	800	
N7890	8,8	780	235,5	9	800	
N8190	9	810	245	9	800	100/100
N1090	9	1020	295	9	800	
N1290	9	1220	375,5	9	800	
N1590	9	1530	460	9	800	



file n° E 223175

HALOGEN

FREE



UV
RESISTANT

BM SPA - Viale Milano 54/56 - 20089 Rozzano (MI) Italy



Technical sheet

No. 78NA01A

Issue V01.0

Product family:

Electrical tapes - PVC electrical tape

Item code:

ESB1510BI, ESB1510BL, ESB1510GI, ESB1510GR, ESB1510GV, ESB1510MA, ESB1510NE, ESB1510RO, ESB1510VE, ESB1525BI, ESB1525BL, ESB1525GI, ESB1525GR, ESB1525GV, ESB1525MA, ESB1525NE, ESB1525RO, ESB1525VE, ESB1925BI, ESB1925BL, ESB1925GI, ESB1925GR, ESB1925GV, ESB1925MA, ESB1925NE, ESB1925RO, ESB1925VE, ESB2525BI, ESB2525BL, ESB2525GI, ESB2525GR, ESB2525GV, ESB2525MA, ESB2525NE, ESB2525RO, ESB2525VE

Description:

ELECTRICAL TAPE · PVC · 0.15 THICKNESS

Image



Specifications

MATERIAL:

PVC

RESISTANT TO:

acids, weathering, corrosion, alkalis, oil, humidity

OPERATING TEMPERATURE:

0°C - +90°C

TENSILE STRENGTH:

28 N/cm equivalent to 18.6 N/mm²

ELONGATION:

200

ADHESION TO STEEL:

2.2

ADHESION TO BACKING:

2

DIELECTRIC STRENGTH:

45

DIELECTRIC STRENGTH:

45 kV/mm

ACCORDING TO STD.:

IEC 60454-2

FLAMMABILITY:

flame retardant

CLASSIFICATION:

EN 60454-3-1-5/F-PVCP/90

ACCORDING TO STD.:

IEC 60454-2

Code	Color	Thickness (mm)	Height (mm)	Length (m)	
ESB1510BI	 White	0,15	15	10	10/200
ESB1510BL	 Blue	0,15	15	10	
ESB1510GI	 Yellow	0,15	15	10	
ESB1510GR	 Grey	0,15	15	10	
ESB1510GV	 YellowGreen	0,15	15	10	
ESB1510MA	 Brown	0,15	15	10	
ESB1510NE	 Black	0,15	15	10	
ESB1510RO	 Red	0,15	15	10	
ESB1510VE	 Green	0,15	15	10	10/100
ESB1525BI	 White	0,15	15	25	
ESB1525BL	 Blue	0,15	15	25	
ESB1525GI	 Yellow	0,15	15	25	
ESB1525GR	 Grey	0,15	15	25	
ESB1525GV	 YellowGreen	0,15	15	25	
ESB1525MA	 Brown	0,15	15	25	
ESB1525NE	 Black	0,15	15	25	
ESB1525RO	 Red	0,15	15	25	10/100
ESB1525VE	 Green	0,15	15	25	
ESB1925BI	 White	0,15	19	25	
ESB1925BL	 Blue	0,15	19	25	
ESB1925GI	 Yellow	0,15	19	25	
ESB1925GR	 Grey	0,15	19	25	
ESB1925GV	 YellowGreen	0,15	19	25	
ESB1925MA	 Brown	0,15	19	25	
ESB1925NE	 Black	0,15	19	25	10/100
ESB1925RO	 Red	0,15	19	25	
ESB1925VE	 Green	0,15	19	25	
ESB2525BI	 White	0,15	25	25	
ESB2525BL	 Blue	0,15	25	25	
ESB2525GI	 Yellow	0,15	25	25	
ESB2525GR	 Grey	0,15	25	25	
ESB2525GV	 YellowGreen	0,15	25	25	
ESB2525MA	 Brown	0,15	25	25	8/80
ESB2525NE	 Black	0,15	25	25	
ESB2525RO	 Red	0,15	25	25	
ESB2525VE	 Green	0,15	25	25	



FLAME
RETARDANT

BM SPA - Viale Milano 54/56 - 20089 Rozzano (MI) Italy