



Continuous Rating	50Amps 50VDC Max.		Circuit Diagram	
Intermittent Rating	75 Amps		OFF	ON
Cranking Rating	300 Amps 5 sec.			
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min			
Dielectric Strength	AC 1000V 1 minute, DC 2000V 1 minute			
Operation Temperature	-30°C~+60°C			
Switch Function	2P SPST OFF-ON	Panel Thickness:9.5mm Max.		



***MATERIAL:**

Housing: Black, PA#66+33%GF

Actuator: Red, PBT+15%GF with white hot stamping





Name Plate: White, ABS with black hot stamping

Bottom: Black, PBT+15%GF

Nut: Black, POM

Screw: Ni-plated, Brass

1 HEX NUT ASSY



tolerances Unless otherwise specified ± 0.3

C3\WORK14\A23-6B

3/24/'21	林珮呈	機種標示更新，原鑄機種A23-6修改為鑄機種A23-6B(ECR#RAD20210303-095)				△
Date	Name	Descriptions				NO
Drawn	Checked	Approved	SCI BOM No.	1340042	Model Name	Battery SWITCH
林珮呈	許庭碩	余欽明	Customer No.		Model No.	A23-6B
3/24/'21	2021/04/01	2021/04/01	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	REV. 1