




PART NUMBER: USB-07-△

"△"	CRUST COLOR
NO LETTER	SILVER
BK	BLACK
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

- 1.OPERATION TEMPERATURE: -25℃~ +55℃ (NO FREEZING) .
- 2.OPERATION HUMIDITY: 45~ 85%RH (NO CONDENSATION) .
- 3.TRANSMISSION RATE: ≥30MB/s.
- 4.HEAD PORT: DOUBLE USB2.0 A TYPE FEMALE.
- 5.BACK PORT: DOUBLE USB2.0 A TYPE FEMALE.

MATERIAL:

- 1.BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE USB2.0 CONNECTOR			UNIT 单位	mm
DWG NO. 图号	USB-07			SCALE 比例	1.2 : 1
FILE NAME 档案名称	金属转接器 USB2.0.DWG	DRAWN 制图	YDY 2022/07/01	SHEET 张	1/1
				REV. 更改	1