

STS1370 ESD-VAC Cleanroom Vacuum Cleaner



Product description:

- Noise level 54 db (lowest setting)
- Four-times filter system with micro fleece dust bag, permanent fine dust filter, motor protection filter, HEPA filter (H 13) at the air outlet
- Special filter bag for dust class L
- 8 l usable bag volume
- Circumferential bumper as protection against damage
- Chassis with 5 conductive castors
- One-handed case release
- Accessory holder and suction tube parking
- Accessory holder with crevice nozzle and upholstery nozzle (removable)
- Cable holder to store the cable, retractable
- Operating radius 15 m approx.

specifications:

protection class:	1	max. air flow:	31 l / sec
power supply:	220 - 240 V / 50 Hz	weight:	5.9 kg
material:	PP-ESD	cable length:	12 m
performance:	900 W	dimensions:	370 x 370 x 380 mm

The information contained within this spec sheet is for guidance only.

We make no warranties expressed or implied and assume no liability regarding any use of this information.



scope of delivery:

1 x Dry tub vac
1 x Suction hose with handle 2.5 m
2 x Suction tubes, 0.50 m each
1 x Hard floor nozzle
1 x Upholstery nozzle
1 x Crevice nozzle

accessories:

Permanent fine dust filter
Micro fleece dust bag
HEPA filter (H13)

We hereby certify that our products;

are compliant with IPC regulations, IEC 61340-5-1-ESD and ANSI/ESD S541

are compliant with all requirement and exemption set by the European RoHS 2.0, Directive 2011/65/EU & the European Delegated Directive (EU) 2015/863.

are compliant with the related requirements of European Union Regulation (EC) 1907/2006 concerning the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH)